

SKINDICHT® SM-M

SKINDICHT® SM-M, metric counter nuts for through-holes on thin-walled housings

Info

Also available as lead-free version - the lead-free articles end on LF after the article number



Good chemical resistance



Mechanical resistance

Application range

Used when a gland has to be countered, or in through-holes on thin-walled housings

Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 Class-Description: Locknut for cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000940

ETIM 6.0 Class-Description: Locknut for cable screw gland

Material:

Nickel-plated brass

Temperature range:

-60°C to +200°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.



SKINDICHT® SM-M

| Article number | Article designation / size | Thickness (mm) | SW wrench size mm | Outer Ø (mm) | Pieces / PU |
|---|----------------------------|----------------|-------------------|--------------|-------------|
| SKINDICHT® SM-M | | | | | |
| 52102998 | M 6 x 1 | 3.2 | 10 | 11.1 | 50 |
| 52102997 | M 8 x 1 | 4.0 | 13 | 14.4 | 50 |
| 52102999 | M 10 x 1 | 5.0 | 17 | 19.1 | 50 |
| 52103000 | M 12 x 1,5 | 3.0 | 15 | 16.5 | 100 |
| 52103010 | M 16 x 1,5 | 3.0 | 19 | 20.9 | 100 |
| 52103020 | M 20 x 1,5 | 3.5 | 24 | 26.4 | 100 |
| 52103030 | M 25 x 1,5 | 4.0 | 30 | 33.0 | 100 |
| 52103040 | M 32 x 1,5 | 4.0 | 36 | 39.6 | 100 |
| 52103050 | M 40 x 1,5 | 5.0 | 46 | 50.6 | 50 |
| 52103060 | M 50 x 1,5 | 5.0 | 60 | 65.0 | 50 |
| 52103070 | M 63 x 1,5 | 5.0 | 70 | 77.0 | 25 |
| 52103071 | M 75 x 1,5 | 8.0 | 85 | 95.0 | 1 |
| 52103072 | M 90 x 2 | 10.0 | 102 | 114.0 | 1 |
| 52103073 | M 110 x 2 | 12.0 | 124 | 135.0 | 1 |
| SKINDICHT® SM-M - Lead-free brass version | | | | | |
| 52103000LF | M 12 x 1,5 | 3.0 | 15 | 16.5 | 100 |
| 52103010LF | M 16 x 1,5 | 3.0 | 19 | 20.9 | 100 |
| 52103020LF | M 20 x 1,5 | 3.5 | 24 | 26.4 | 100 |
| 52103030LF | M 25 x 1,5 | 4.0 | 30 | 33.0 | 100 |
| 52103040LF | M 32 x 1,5 | 4.0 | 36 | 39.6 | 100 |
| 52103050LF | M 40 x 1,5 | 5.0 | 46 | 50.6 | 50 |
| 52103060LF | M 50 x 1,5 | 5.0 | 60 | 65.0 | 50 |
| 52103070LF | M 63 x 1,5 | 5.0 | 70 | 77.0 | 25 |

Last Update (18.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16