


## SKINDICHT® SRE-M

SKINDICHT® SRE-M, metric cable gland with perfect seal with anti-kink protection, high degree of protection and cable-protecting strain relief



Mechanical resistance



Optimum strain relief



Interference signals

### Benefits

- Perfect seal with anti-kink protection
- Optimum, low-resistance 360° screen contact
- Cable-protecting strain relief
- Gentle cable clamping
- High degree of protection

### Application range

Earthing gland with additional anti-kink protection. For applications where electrical interference fields can occur.

- Moving machine parts
- Conveyor and transport systems
- Production lines
- Measurement and control technology

### Product Make-up

Metric connection thread acc. to DIN EN 60423  
Basis for technical information DIN IEC 62444

### Note

SKINDICHT® SM-PE-M counter nut should be used to ensure optimum contact with painted, anodised or powder-coated housings  
Example description:  
SRE-M 20/13.5/9/6

Last Update (15.02.2026)

©2026 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SKINDICHT® SRE-M

20 = metric connection thread  
13.5 = PG function thread  
9 = clear opening of anti-kink sleeve (F)  
6 = clear opening of earthing sleeve (B)

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Caution:	The installation dimensions can be found in appendix T21
On request:	Available with long connection thread
Material:	Body: nickel-plated brass Earthing sleeve: plain brass Anti-kink sleeve: CR/NBR O-ring: NBR
Protection rating:	IP 65
Temperature range:	-20°C to +80°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINDICHT® SRE-M**

Article number	Article designation / size	Function thread PG	Outer sheath clamping range ØF mm	Inner sheath clamping range (mm)	SW1/SW2 mm	Overall length C mm	Thread length D mm	Clear opening earthing sleeve ØB	Clear opening F (mm)	Pieces / PU
SKINDICHT® SRE-M										
52105600	M 20 x 1,5	13.5	7.5 - 9	4.5 - 6	22 / 22	59.5	6	6	9.0	25
52105610	M 20 x 1,5	13.5	9 - 11	5.5 - 7	22 / 22	59.5	6	7	11.0	25
52105620	M 20 x 1,5	16	11 - 13	7 - 9	24 / 24	64.5	6	9	13.0	25
52105630	M 20 x 1,5	16	11 - 13	8 - 10	24 / 24	64.5	6	10	13.0	25
52105640	M 20 x 1,5	16	13.5 - 15	9 - 11	24 / 24	64.5	6	11	15.0	25
52105650	M 25 x 1,5	21	13.5 - 15	10 - 12	30 / 30	78.0	7	12	15.0	25
52105660	M 25 x 1,5	21	15 - 17	12 - 14	30 / 30	78.0	7	14	17.0	25
52105670	M 25 x 1,5	21	17 - 19	13 - 15	30 / 30	78.0	7	15	19.0	25
52105680	M 25 x 1,5	21	18 - 20	14 - 16	30 / 30	78.0	7	16	20.0	25
52105690	M 32 x 1,5	29	18 - 20	15 - 17	40 / 40	90.0	8	17	20.0	10
52105700	M 32 x 1,5	29	21 - 23	17 - 19	40 / 40	90.0	8	19	23.0	10
52105710	M 40 x 1,5	36	23.5 - 26	20 - 22	50 / 50	108.0	8	22	26.0	5
52105720	M 40 x 1,5	36	27 - 30	22 - 24	50 / 50	108.0	8	24	30.0	5
52105730	M 40 x 1,5	36	30 - 33	26 - 28	50 / 50	108.0	8	28	33.0	5
52105740	M 40 x 1,5	36	32 - 35	28 - 30	50 / 50	108.0	8	30	35.0	5

Last Update (15.02.2026)

©2026 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

 You can find the current technical data in the corresponding data sheet.  
 PN 0456 / 02\_03\_16