
# SKINTOP® MS-SC

SKINTOP® MS-SC, brass cable gland with low-resistance screen contact and highly conductive, flexible EMC contact, easy to assemble







- Optimum strain relief
- Robust
- Interference signals
- Temperature-resistant
- Variety of approval certifications

## Benefits

Low-resistance screen contact, optimum EMC protection
Suitable for cables with and without inner sheath
Also suitable for continuing the cable screen to another connection
Highly conductive, flexible EMC contact for clamping various screen diameters
Few operation steps, easy to assemble

## Application range

For EMC-compliant earthing of the copper braiding
Telecommunication
Industrial machinery and plant engineering
Measurement and control technology
Automation technology

## Product Make-up

PG connection thread acc. to DIN 40430

Last Update (16.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

# SKINTOP® MS-SC

## Note
EMC counter nut, SKINDICHT® SM nut should be used to ensure optimum contact with painted, anodised or powder-coated housings

## Technical Data

| | |
|---|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000441<br>ETIM 5.0 Class-Description: Cable screw gland |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000441<br>ETIM 6.0 Class-Description: Cable screw gland |
| Caution: | Refer to Appendix T21 for the installation dimensions and torques |
| Material: | Body: nickel-plated brass<br>Insert: polyamide<br>Sealing: CR<br>O-ring: NBR |
| Protection rating: | IP 68 - 5 bar |
| Temperature range: | Dynamic: -25 °C up to +100 °C<br>Fixed: -40 °C to +100 °C |

## Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.


©2025 Lapp Group - Technical changes reserved

LAPP


# SKINTOP® MS-SC


PRODUCT INFORMATION


| Article number | Article designation / size | Ø F mm | Minimum Ø above braiding (mm) | SW wrench size mm | Overall length C mm | Thread length D mm | Pieces / PU |
|---|---|---|---|---|---|---|---|
| SKINTOP® MS-SC | | | | | | | |
| 53112210 | PG 9 | 3.0 - 8.0 | 4 | 17 | 29.0 | 6 | 50 |
| 53112220 | PG 11 | 4.0 - 10.0 | 4 | 20 | 32.0 | 6 | 50 |
| 53112230 | PG 13,5 | 5.0 - 12.0 | 4 | 22 | 34.0 | 6.5 | 25 |
| 53112240 | PG 16 | 8.0 - 14.0 | 6 | 24 | 35.0 | 6.5 | 25 |
| 53112250 | PG 21 | 11.0 - 18.0 | 8 | 30 | 40.0 | 7 | 25 |
| 53112260 | PG 29 | 16.0 - 25.0 | 13 | 40 | 48.0 | 8 | 10 |
| 53112270 | PG 36 | 19.0 - 32.0 | 16 | 50 | 62.0 | 15 | 5 |
| SKINTOP® MS-SC XL | | | | | | | |
| 53112310 | PG 9 | 3.0 - 8.0 | 4 | 17 | 35.0 | 12 | 50 |
| 53112320 | PG 11 | 4.0 - 10.0 | 4 | 20 | 38.0 | 12 | 50 |
| 53112330 | PG 13,5 | 5.0 - 12.0 | 4 | 22 | 39.5 | 12 | 25 |
| 53112340 | PG 16 | 8.0 - 14.0 | 6 | 24 | 40.5 | 12 | 25 |
| 53112350 | PG 21 | 11.0 - 18.0 | 8 | 30 | 45.0 | 12 | 25 |
| 53112360 | PG 29 | 16.0 - 25.0 | 13 | 40 | 52.0 | 15 | 10 |

Last Update (16.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

# SKINTOP® MS-SC








Last Update (16.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16