


## SKINTOP® MS-M BRUSH

SKINTOP® MS-M BRUSH, brass cable gland with double lamella gasket, faster, low resistance 360° screen contact, simple assembling

### Info

NEW: Now also available in size M20x1.5

SKINTOP® MS-M sizes 75 x 1.5 to 110 x 2 with innovative double lamella gasket for easier assembling of cables with large diameters.



Reliability



Voltage



Interference signals



Temperature-resistant

### Benefits

Optimum, low-resistance 360° screen contact  
Faster than any other comparable system  
Also suitable for continuing the cable screen to another connection  
Uncomplicated and reliable  
Maximum assembly freedom during adjustment

### Application range

For EMC-compliant earthing of the copper braiding  
Automation systems  
High-power drives  
Frequency converters  
Conveyor and transport systems

Last Update (18.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SKINTOP® MS-M BRUSH

### Norm references / Approvals

UL File Nr. E79903

### Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

### Note

SKINDICHT® SM-PE-M counter nut should be used to ensure optimum contact with painted, anodised or powder-coated housings

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Caution:	Refer to Appendix T21 for the installation dimensions and torques
Material:	Body: nickel-plated brass Cap nut: nickel-plated brass Insert: polyamide EMC brush: brass wire Sealing ring: elastomer O-ring: elastomer
Protection rating:	IP 68 - 10 bar (M12 - M110) IP 69 (M12 - M63) NEMA Type 1, 4x, 6, 12
Temperature range:	Dynamic: -25°C up to +100°C Fixed: -40°C to +100°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINTOP® MS-M BRUSH**

Article number	Article designation / size	Outer Ø (mm), from - to	Minimum Ø above braiding (mm)	SW wrench size mm	Thread length D mm	Pieces / PU
<b>SKINTOP® MS-M BRUSH</b>						
53112507	M 20 x 1,5	7.0 - 13.0	3	24	8	25
53112676	M 25 x 1,5	9.0 - 17.0	6	29	8	10
53112677	M 32 x 1,5	11.0 - 21.0	8	36	9	5
53112678	M 40 x 1,5	19.0 - 28.0	10	45	9	5
53112679	M 50 x 1,5	27.0 - 35.0	14	54	10	5
53112680	M 63 x 1,5	34.0 - 45.0	20	67	15	1
53112681	M 63 x 1,5 plus	44.0 - 55.0	25	75	15	1
53112501	M 75 x 1,5	53.0 - 63.0	25	95	15	1
53112500	M 75 x 1,5 plus	58.0 - 68.0	25	95	15	1
53112503	M 90 x 2	66.0 - 78.0	40	115	20	1
53112505	M 110 x 2	76.0 - 88.0	50	135	25	1
53112504	M 110 x 2 plus	86.0 - 98.0	50	135	25	1
<b>SKINTOP® MS-M BRUSH XL</b>						
53112527	M 20 x 1,5	7.0 - 13.0	3	24	12	25
53113727	M 25 x 1,5	9.0 - 17.0	6	29	12	10
53113728	M 32 x 1,5	11.0 - 21.0	8	36	15	5
53113729	M 40 x 1,5	19.0 - 28.0	10	45	15	5
53112673	M 50 x 1,5	27.0 - 35.0	14	54	15	5

Last Update (18.12.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

 You can find the current technical data in the corresponding data sheet.  
 PN 0456 / 02\_03\_16

## SKINTOP® MS-M BRUSH

