

EPIC® SIGNAL M23 D6

Circular connectors for Servo Cables and encoders

EPIC® M23 cable connector signal with coupling nut

Info

Robust metal connector with integrated EMC cable gland

Made in Germany



Mechanical and plant engineering



Wind Energy



Good chemical resistance



Optimum strain relief



Robust



Integrated SKINTOP[®] cable gland



Interference signals

Benefits

Low-resistance screen contact, optimum EMC protection

Use of high quality materials for increased reliability

Last Update (25.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® SIGNAL M23 D6

Application range

Plant engineering
Servo drives and servo assemblies
Measurement and control technology

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: nickel-plated zinc die-casting Sealing: FPM
Protection rating:	IP68 (10h/1m)
VDE-tested:	Certified production control: VDE-REG. no. C24 (according to EN 61984, SELV according to DIN VDE 0100-410 has to be guaranteed) UL File Number: E249137
Temperature range:	-25 °C up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® SIGNAL M23 D6

Article number	Article	Coding	Cable clamping range	Pieces / PU
Type M23 D6 cable connector				
44420037	M23 D6	black (N)	7 - 13.5	5
75018413	M23 D6	black (N)	5.0 - 7.3	5
72044030	M23 D6	black (N)	7 - 10	5
72044020	M23 D6	black (N)	7 - 10	20
72044000	M23 D6	black (N)	9.5 - 13.5	5
72044010	M23 D6	black (N)	9.5 - 13.5	20
44420038	M23 D6	red (+20°)	7 - 13.5	5
72044230	M23 D6	red (+20°)	7 - 10	5
72044220	M23 D6	red (+20°)	7 - 10	20
72044200	M23 D6	red (+20°)	9.5 - 13.5	5
72044210	M23 D6	red (+20°)	9.5 - 13.5	20
44420036	M23 D6	blue (-20°)	7 - 13.5	5
72044130	M23 D6	blue (-20°)	7 - 10	5
72044120	M23 D6	blue (-20°)	7 - 10	20
72044100	M23 D6	blue (-20°)	9.5 - 13.5	5
72044110	M23 D6	blue (-20°)	9.5 - 13.5	20

Last Update (25.12.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

EPIC® SIGNAL M23 D6

