

SILVYN® KLICK PG

SILVYN® KLICK PG - PG threaded conduit fitting for SILVYN® RILL



Assembly time



Temperature-resistant



Variety of approval certifications

Benefits

- Fast assembly
- Easy to disassemble
- High-tensile
- High sealing performance
- Can be rotated

Application range

In combination with protective conduit:
SILVYN® RILL PA 6
SILVYN® RILL PA 12
Robot-building
Rotating applications

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

- PG connection thread
- Body with inner sealing
- Upper part with snap-in sleeve

Last Update (20.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® KLICK PG**Technical Data**

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Colour delivered:	Grey (RAL 7031) Black (RAL 9011), UV-resistant
Material:	PA6 Halogen-free
Protection rating:	IP 68 IP 69
Temperature range:	-40 °C to +115 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



SILVYN® KLICK PG

Article number	PG size	SW wrench size mm	Overall length mm	Thread length mm	Clear opening (mm)	For conduit with outer Ø (mm)	Suitable for SILVYN® RILL	Pieces / PU
SILVYN® KLICK PG grey								
61800860	7	16	32.5	10	7	10	10	50
61800870	9	18	35	10	10	13	13	50
61800880	11	21	37	10	12.5	15.8	16	50
61800850	13.5	24	43	13	13.5	18.5	18	50
61800890	16	27	46	13	17	21.2	21	50
61800900	21	34	48.5	13	23.5	28.5	28	25
61800910	29	40	53.5	14.5	30	34.5	34	25
61800920	36	60	76	17	36	42.5	42	25
61800930	48	70	88	17	47.5	54.5	54	10
SILVYN® KLICK PG black								
61800865	7	16	32.5	10	7	10	10	50
61800875	9	18	35	10	10	13	13	50
61800885	11	21	37	10	12.5	15.8	16	50
61800855	13.5	24	43	13	13.5	18.5	18	50
61800895	16	27	46	13	17	21.2	21	50
61800905	21	34	48.5	13	23.5	28.5	28	25
61800915	29	40	53.5	14.5	30	34.5	34	25
61800925	36	60	76	17	36	42.5	42	25
61800935	48	70	88	17	47.5	54.5	54	10

Last Update (20.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16