# DATA SHEET


Valid from: 30.01.2020

EPIC<sup>®</sup> MHS 24 R MULTI-FRAME



### Description

- Multi- frame for recording own and third-party modules
- EPIC<sup>®</sup> MH system is pluggable with the market standard
- The mixing of various functions in one connector ensures a high degree of flexibility
- PE Connection from 1mm<sup>2</sup> to 6mm<sup>2</sup> with wire end ferrule, 10mm<sup>2</sup> with adapter
- Use for railway applications -Brand protection in rail vehicles: test according to EN 45545-2. Requirement sentences R22 and R23. Hazard levels HL1, HL2 and HL3



### **General Characteristics**

Product description Series Version Number of Modules EPIC<sup>®</sup> MHS 24 R (A, B, C, D, E, F) MH Multi-frame Male 6

#### Surfaces

Frame

Zinc die casting alloy

### Standard

Safety Standard

IEC 61984

	Creator: ERTC1/PDP	Document: DB44423240EN	Page 1 of 2	
	Released: IVSE1/PDP	Version: 02		

# **DATA SHEET**




EPIC<sup>®</sup> MHS 24 R MULTI-FRAME



### **Technical Drawing**







Automation



Industrial machinery and plant engineering

Wind Energy

### Info

Frame system for modules Various functions can be used together in one connector

### **Product features**

The MCR "male" frame version is designed for use with modules with male contacts; the "female" version is designed for use with modules with female contacts. The high design is to be used for sleeve housings

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: ERTC1/PDP	Document: DB44423240EN	Page 2 of 2		
Released: IVSE1/PDP	Version: 02			
We recently all rights according to DIN ICO 10010				