# DATA SHEET

EPIC® MHB 24 R MULTI-FRAME




## Description

Valid from:

30.01.2020

- Multi- frame for recording own and third-party modules
- EPIC® MH system is pluggable with the market standard
- The mixing of various functions in one connector ensures a high degree of flexibility
- PE Connection from 1mm<sup>2</sup> to 6mm<sup>2</sup> with wire end ferrule, 10mm<sup>2</sup> with adapter
- Use for railway applications -Brand protection in rail vehicles: test according to EN 45545-2. Requirement sentences R22 and R23. Hazard levels HL1, HL2 and HL3



### **General Characteristics**

Product description EPIC® MHB 24 R (a, b, c, d, e, f)

Series MH Multi-frame

Version Female Number of Modules 6

### **Surfaces**

Frame Zinc die casting alloy

### Standard

Safety Standard IEC 61984

# 44423241

# DATA SHEET


# **& LAPP**

Valid from: 30.01.2020

# **EPIC® MHB 24 R MULTI-FRAME**

## **Technical Drawing**







Automation



Industrial machinery and plant engineering



Wind Energy

#### Info

Frame system for modules

Various functions can be used together in one connector

#### **Product features**

The MCR "male" frame version is designed for use with modules with male contacts; the "female" version is designed for use with modules with female contacts. The high design is to be used for sleeve housings

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: ERTC1/PDP	Document: DB44423241EN	Page 2 of 2
Released: IVSE1/PDP	Version: 02	