44423234

DATA SHEET


& LAPP

Valid from: 30.01.2020

EPIC® MHS 6 MULTI-FRAME

Description

- Multi- frame for recording own and third-party modules
- EPIC® MH system is pluggable with the market standard
- The mixing of various functions in one connector ensures a high degree of flexibility
- PE Connection from 1mm2 to 6mm2 with wire end ferrule, 10mm2 with adapter
- Use for railway applications -Brand protection in rail vehicles: test according to EN 45545-2. Requirement sentences R22 and R23. Hazard levels HL1, HL2 and HL3



General Characteristics

Product description EPIC® MHS 6 R (A, B)
Series MH Multi-frame

Version Male Number of Modules 2

Surfaces

Frame Zinc die casting alloy

Standard

Safety Standard IEC 61984

44423234


DATA SHEET


Valid from: 30.01.2020


EPIC® MHS 6 MULTI-FRAME



Technical Drawing









Automation



Industrial machinery and plant engineering



Wind Energy

Info

Frame system for modules Various functions can be used together in one connector

Product features

The MCR "male" frame version is designed for use with modules with male contacts; the "female" version is designed for use with modules with female contacts. The high design is to be used for sleeve housings

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

| Creator: ERTC1/PDP | Document: DB44423234EN | Page 2 of 2 |
|---------------------|------------------------|-------------|
| Released: IVSE1/PDP | Version: 02 | |