

SKINDICHT® BL-M hex. FKM

SKINDICHT® BL-M, brass blind plugs hexagonal with FKM o-ring for closing pre-threaded holes, assembling with open-end wrench



Mechanical and plant engineering



Oil & Gas



Good chemical resistance



Heat-resistant



Corrosion-resistant



Mechanical resistance



Assembly time



Oil-resistant



Robust



Reliability



Temperature-resistant

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® BL-M hex. FKM

Benefits

Withstands temperatures up to +200 °C.

Simple assembly by using an open-end wrench.

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future according to the RoHS Directive.

Application range

For closing an unoccupied metric threaded hole on the housing.

Withstands high chemical and mechanical stress.

Product features

Assembling with open-end wrench.

Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000032 ETIM 5.0 Class-Description: Plug for cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000032 ETIM 6.0 Class-Description: Plug for cable screw gland
Material:	Body: nickel-plated brass O-Ring: FKM
Protection rating:	IP 66 IP 68 - 10 bar
Temperature range:	-20 °C to +200 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® BL-M hex. FKM

Article number	Article designation / size	SW wrench size mm	Overall length C mm	Thread length D mm	Pieces / PU
52006118	M12x1,5	16	8.0	5	25
52103479	M16x1,5	20	8.0	5	25
52103426	M20x1,5	24	9.5	6	25
52103436	M25x1,5	29	11.0	7	25
52103480	M32x1,5	36	12.0	8	25
52103481	M40x1,5	45	13.0	8	25
52103466	M50x1,5	54	15.0	9	5
lead free brass version					
52103406LF	M12x1,5	16	8.0	5	25
52103416LF	M16x1,5	20	8.0	5	25
52103426LF	M20x1,5	24	9.5	6	25
52103436LF	M25x1,5	29	11.0	7	25
52103446LF	M32x1,5	36	12.0	8	25
52103456LF	M40x1,5	45	13.0	8	25
52103466LF	M50x1,5	54	15.0	9	5
52103476LF	M63x1,5	67	16.0	10	5
52103476	M63x1,5	67	16.0	10	5

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03_16