2170261

DATA SHEET

valid from: 01.01.2019 UNITRONIC® BUS CAN A

2 x 2 x 0,22 mm²



Application

UNITRONIC[®] BUS CAN A is a data cable with UL and cUL approval, for CAN (Controller Area Network) fieldbus system according To ISO11898 as well as for high performance data networks with 120 Ohms nominal impedance. The second pair can be used for electrical power supply for the logical bus units. The transmission characteristics of the cable conform to the CAN system and guarantee a high operating security during data transmission. The possible data transmission acc. to ISO 11898 for max. 40m is 1 Mbit/s. UNITRONIC[®] BUS A is intended for permanent installation and conditional flexible use in dry and damp interiors.

Design

Certification	UL / cUL type CMX according to UL 444 and CSA C22.2 No.214-02.
Conductor	seven-wire strands of bare copper, 0.22mm ² , (24AWG)
Insulation	cellular PE or foam skin, core diameter approx. 1.4 mm
Core identification code	pair 1 white and brown, pair 2 green and yellow (acc. DIN 47100)
Stranding	2 cores twisted into pairs, 2 pairs arranged to the cable core plastic foil
Screen	braid of tinned copper wires
Outer sheath	PVC, violet, OD approx. 7.5 mm
Electrical properties at 20°C	
Loop resistance	max. 186 Ω/km
Insulation resistance	min. 5 GΩxkm
Mutual capacitance	nom. nF/km 40
Characteristic impedance	at f \geq 1 MHz Ω 120 ± 15%
Attenuation	 100 kHz nom. dB/100 m 0,6 1 MHz nom. dB/100 m 1,7 5 MHz nom. dB/100 m 3,9 10 MHz nom. dB/100 m 5,6 20 MHz nom. dB/100 m 8,1
Near-end cross-talk	1 MHz min. dB 50 20 MHz min. dB 40
Velocity of propagation	nom. 76 %
Signal transit time	4,4 ns/m
Transfer impedance	at 30 MHz max. 250 m Ω/m
Peak operating voltage	250 V (not for power applications)
Test voltage	conductor/conductor 1500 V conductor/screen 1000 V

 Creator:
 TOST / PDC
 Document:
 DB2170261EN
 Page 1 of 2

 Released:
 ALTE / PDC
 Version:
 04
 Page 1 of 2

valid from: 01.01.2019

DATA SHEET

UNITRONIC® BUS CAN A

2 x 2 x 0,22 mm²



Mechanical and thermal properties

Minimum bending radius	moved: 10 x cable Ø
Temperature range	moved -5° C to $+70^{\circ}$ C static -30° C to $+80^{\circ}$ C
Flammability	flame retardant to VDE 0482, part 265-2-1 / IEC 60332-1
General requirements	This cable is conform to the EU-Directive 2011/65/EU (RoHS, Restriction of the use of certain hazardous substances).

Creator:TOST / PDCDocument:DB2170261ENReleased:ALTE / PDCVersion:04

Page 2 of 2