SKINTOP® CLICK BLK

SKINTOP® CLICK BLK, blind plug with innovative CLICK system, counter nut and thread not required, captive, simple, free assembly



Assembly time

Robust

Reliability

Benefits

Save up to 70% of the time with the innovative CLICK system
Simple, free assembly in any position
Fewer parts, counter nut no longer needed
No thread required

Application range

Dummy plug with innovative CLICK system for fast installation in hard-to-reach locations. Perfect solution for closing pre-made bore holes that are no longer required.
Control cabinet manufacturing
Measurement, control and electrical applications
Automation technology
Plant engineering, machinery manufacturing

Included

Included: disassembly tool

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441
ETIM 5.0 Class-Description: Cable screw gland

©2025 Lapp Group - Technical changes reserved

SKINTOP® CLICK BLK

Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Colour delivered:	Light grey (RAL 7035)
Material:	Body: special polyamide Seal: special elastomer
Protection rating:	IP 68 - 5 bar
Temperature range:	-20 °C to +100 °C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2025 Lapp Group - Technical changes reserved

LAPP

SKINTOP® CLICK BLK

PRODUCT INFORMATION

Article number	Article designation / size	M (hole in mm)	SW1/SW2 mm	Overall length C mm	Thread length D mm	Wall thickness, S (mm)	Pieces / PU
SKINTOP® CLICK BLK light grey							
52109013	CLICK BLK 16	16.3 (-0.2)	14.0 / 22.0	28.5	8	1.0 - 4.0	50
52109014	CLICK BLK 20	20.3 (-0.2)	18.0 / 27.0	29.5	8	1.0 - 4.0	25
52109015	CLICK BLK 25	25.3 (-0.2)	22.0 / 14.0	30.5	8	1.0 - 4.0	25

Last Update (16.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16