

SKINDICHT® SM-PE

SKINDICHT® SM-PE, counter nut with cutting edges to cut through the insulating layer, for glands used in EMC applications



Benefits

Cutting edges cut through the insulating layer, thus guaranteeing an optimum EMC contact

Application range

For lacquered, anodised or powder-coated housings.

Product Make-up

PG connection thread

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 Class-Description: Locknut for cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000940

ETIM 6.0 Class-Description: Locknut for cable screw gland

Material:

Nickel-plated brass

Temperature range:

-60 °C to +200 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® SM-PE

Article number	Article designation / size	Height (mm)	SW wrench size mm	Far corner dimension	Pieces / PU
SKINDICHT® SM-PE					
52103200	PG 7	4.7	15	17.3	100
52103210	PG 9	4.7	18	20.8	100
52103220	PG 11	4.7	21	24.3	100
52103230	PG 13,5	4.7	23	26.6	100
52103240	PG 16	4.7	26	30	100
52103250	PG 21	5.2	32	37	50
52103260	PG 29	5.7	41	47.3	50
52103270	PG 36	6.5	51	58.9	50

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16