

SKINDICHT® EV

SKINDICHT® EV, incised sealing rings for high temperatures, resistant to oils, solvents, acids and chemicals



Temperature-resistant

Benefits

One seal for several clamping ranges
The various incisions can be easily taken out with a knife.
For high temperatures
Resistant to oils, solvents, acids and chemicals

Application range

Incised sealing ring made of FKM for SKINDICHT® cable glands

Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001181 ETIM 5.0 Class-Description: Sealing ring
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001181 ETIM 6.0 Class-Description: Sealing ring
Colour delivered:	Red brown
Material:	FKM
Temperature range:	-20 °C to +200 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® EV

Article number	Article designation / size	Outer diameter x bores (mm)	Thickness (mm)	Outer Ø (mm)	Pieces / PU
SKINDICHT® EV					
52010340	EV 11	7/10/12.5	6.0	16.5	50
52010350	EV 13,5	7/10.5/13/16	6.5	18.5	50