

## SKINDICHT® BL-M hex.

SKINDICHT® BL-M, brass blind plugs hexagonal for closing pre-threaded holes, assembling with screwdriver



Temperature-resistant



Reliability



Robust



Corrosion-resistant

### Benefits

For closing pre-threaded holes  
High degree of protection

### Application range

Machine and equipment manufacturing  
Electric motor manufacturing

### Product Make-up

Metric connection thread acc. to DIN EN 60423  
Basis for technical information DIN IEC 62444

### Note

Dummy plug made of chromium nickel steel on request

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000032

ETIM 5.0 Class-Description: Plug for cable screw gland

Last Update (12.07.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**SKINDICHT® BL-M hex.**

|                        |   |
|------------------------|---|
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000032<br>ETIM 6.0 Class-Description: Plug for cable screw gland |
| On request:            | FKM O-ring<br>-20 °C to +200 °C   |
| Material:              | Body: nickel-plated brass<br>O-ring: NBR  |
| Protection rating:     | IP 68 - 5 bar   |
| Temperature range:     | -30°C to +100°C   |

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINDICHT® BL-M hex.**

| Article number       | Article designation / size | SW wrench size mm | PL_DURCHMESSERAUSSE<br>N | Outer Ø (mm) | Pieces / PU |
|----------------------|----------------------------|-------------------|--------------------------|--------------|-------------|
| SKINDICHT® BL-M hex. |                            |                   |                          |              |             |
| 52103405             | M 12 x 1,5                 | 16                | 17.8                     | 17.8         | 50          |
| 52103415             | M 16 x 1,5                 | 20                | 22                       | 22.0         | 50          |
| 52103425             | M 20 x 1,5                 | 24                | 26.4                     | 26.4         | 50          |
| 52103435             | M 25 x 1,5                 | 29                | 31.9                     | 31.9         | 50          |
| 52103445             | M 32 x 1,5                 | 36                | 39.6                     | 39.6         | 25          |
| 52103455             | M 40 x 1,5                 | 45                | 49.5                     | 49.5         | 25          |
| 52103465             | M 50 x 1,5                 | 54                | 59                       | 59.0         | 10          |
| 52103475             | M 63 x 1,5                 | 67                | 73.5                     | 73.5         | 10          |

Last Update (12.07.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16