

SKINDICHT® BL-M

SKINDICHT® BL-M, brass blind plugs for closing pre-threaded holes, assembling with screwdriver



Corrosion-resistant



Robust



Reliability



Temperature-resistant

Benefits

For closing pre-threaded holes

Application range

Machine and equipment manufacturing

Electric motor manufacturing

Product features

Assembling with screwdriver

Norm references / Approvals

UL File Nr. E79903

Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

Technical Data

Last Update (03.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® BL-M

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000032 ETIM 5.0 Class-Description: Plug for cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000032 ETIM 6.0 Class-Description: Plug for cable screw gland
Certifications:	UL File E79903
On request:	Fitted with FKM O-ring (-20°C to +200°C)
Material:	Body: nickel-plated brass O-ring: NBR
Protection rating:	IP 54 IP 68 (with O-ring)
Temperature range:	With O-ring: -20°C to +100°C Without O-ring: -60°C to +200°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® BL-M

Article number	Article designation / size	Overall length C mm	Thread length D mm	Outer Ø (mm)	Pieces / PU
SKINDICHT® BL-M					
52103100	M 12 x 1,5	7.5	5	14.0	100
52103110	M 16 x 1,5	8.0	5	18.0	100
52103120	M 20 x 1,5	9.5	6	22.0	100
52103130	M 25 x 1,5	11.0	7	28.0	100
52103140	M 32 x 1,5	12.0	8	35.0	50
52103150	M 40 x 1,5	13.0	9	44.0	25
52103160	M 50 x 1,5	15.0	9	54.0	10
52103170	M 63 x 1,5	16.0	10	70.0	10
52103190	M 75 x 1,5	17.0	11	80.0	1
SKINDICHT® BL-M with O-ring					
52103105	M 12 x 1,5	7.5	5	14.0	100
52103115	M 16 x 1,5	8.0	5	18.0	100
52103125	M 20 x 1,5	9.5	6	22.0	100
52103135	M 25 x 1,5	11.0	7	28.0	100
52103145	M 32 x 1,5	12.0	8	35.0	50
52103155	M 40 x 1,5	13.0	9	44.0	25
52103165	M 50 x 1,5	15.0	9	54.0	10
52103175	M 63 x 1,5	16.0	10	70.0	10

Last Update (03.09.2020)

©2020 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03_16