

SKINDICHT® EV

SKINDICHT® EV, incised sealing rings for high temperatures, resistant to oils, solvents, acids and chemicals



Temperature-resistant

Benefits

- One seal for several clamping ranges
- Rings can be individually adapted to various cable diameters
- For high temperatures
- Resistant to oils, solvents, acids and chemicals

Application range

Incised sealing ring made of FKM for SKINDICHT® cable glands

Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001181 ETIM 5.0 Class-Description: Sealing ring
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001181 ETIM 6.0 Class-Description: Sealing ring
Colour delivered:	Red brown
Material:	FKM
Temperature range:	-20°C to +200°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (05.07.2019)

©2019 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® EV

Article number	Article designation / size	Outer diameter x bores (mm)	Thickness (mm)	PL_DURCHMESSERAU SSEN	Outer Ø (mm)	Pieces / PU
SKINDICHT® EV						
52010340	EV 11	7/10/12.5	6.0	16.5	16.5	50
52010350	EV 13,5	7/10.5/13/16	6.5	18.5	18.5	50
52010360	EV 16	8/10.5/13.5/16	7.5	20.5	20.5	50
52010370	EV 21	11/15/18/20	8.0	26	26.0	25
52010380	EV 29	19/23/27/31	9.5	35	35.0	25
52010390	EV 36	25/28/31/35	12.0	45	45.0	25
52010410	EV 42	35.5/39/42.5/46	14.0	52	52.0	25

Last Update (05.07.2019)

©2019 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16