


SKINDICHT® RWV-M without E+D

SKINDICHT® RWV-M without E+D, angle cable gland with cable running parallel to the housing wall, corrosion-resistant and combinable









Corrosion-resistant

Space requirement

Connector with standard housing unit

Temperature-resistant

Benefits

Combination of different conduit glands is possible
Space- and weight-saving application due to thin cable diameters
Decrease in installation height
Cable runs parallel to the housing wall
Corrosion-resistant

Application range

Angled glands are used in areas where cables have to run in parallel to the housing wall.
Electric motor manufacturing
Machine and equipment manufacturing
Plant engineering
Light and sound applications

Product Make-up

Metric connection thread acc. to DIN EN 60423
Basis for technical information DIN IEC 62444

Last Update (21.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

SKINDICHT® RWV-M without E+D

Note

The protection class is dependent on the combination with the various special glands. The minimum standard is IP 55.
Counter nut to be used: SKINDICHT® SM-M
For combination with other SKINDICHT® or SKINTOP® cable glands, we propose our SKINDICHT® RWV-M without incised sealing ring (E) and compression screw (D)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Material:	Body: zinc die-casting Hexagon nut: nickel-plated brass O-ring: NBR
Protection rating:	IP 55
Temperature range:	-20 °C to +100 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2023 Lapp Group - Technical changes reserved

LAPP

PRODUCT INFORMATION

SKINDICHT® RWV-M without E+D

Article number	Article designation / size	B in mm	Thread length D mm	K	L	Ø G	SW1	Ø A1	SW2	Ø A2	Pieces / PU
SKINDICHT® RWV-M without E+D											
52107801	M 12 x 1,5	21	11.5	5	20.5	8	14.0	16	17.0	18.9	25
52107811	M 16 x 1,5	23	11.5	5	23.5	12	18.0	20	22.0	24.5	25
52107821	M 20 x 1,5	28.5	12.5	5	28.5	15	22.0	24	27.0	30.1	25
52107831	M 25 x 1,5	30	13.5	5	31	20	27.0	29	32.0	35.7	10
52107841	M 32 x 1,5	36.5	13.5	5	33.5	27	34.0	33.5	41.0	45.6	10
52107851	M 40 x 1,5	43	15.5	5	43	35	42.0	43	46.0	50.6	5

Last Update (21.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16