


SKINDICHT® SRE-M

SKINDICHT® SRE-M, metric cable gland with perfect seal with anti-kink protection, high degree of protection and cable-protecting strain relief



Mechanical resistance



Optimum strain relief



Interference signals

Benefits

- Perfect seal with anti-kink protection
- Optimum, low-resistance 360° screen contact
- Cable-protecting strain relief
- Gentle cable clamping
- High degree of protection

Application range

- Earthing gland with additional anti-kink protection. For applications where electrical interference fields can occur.
- Moving machine parts
- Conveyor and transport systems
- Production lines
- Measurement and control technology

Product Make-up

- Metric connection thread acc. to DIN EN 60423
- Basis for technical information DIN IEC 62444

Note

SKINDICHT® SM-PE-M counter nut should be used to ensure optimum contact with painted, anodised or powder-coated housings
Example description:

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® SRE-M

SRE-M 20/13.5/9/6

20 = metric connection thread

13.5 = PG function thread

9 = clear opening of anti-kink sleeve (F)

6 = clear opening of earthing sleeve (B)

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: Cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class-Description: Cable screw gland

Caution:

The installation dimensions
can be found in appendix T21

On request:

Available with long connection thread

Material:

Body: nickel-plated brass

Earthing sleeve: plain brass

Anti-kink sleeve: CR/NBR

O-ring: NBR

Protection rating:

IP 65

Temperature range:

-20°C to +80°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® SRE-M

Article number	Article designation / size	Function thread PG	Outer sheath clamping range ØF mm	Inner sheath clamping range (mm)	SW1/SW2 mm	Overall length C mm	Thread length D mm	Clear opening earthing sleeve ØB	Clear opening F (mm)	Pieces / PU
SKINDICHT® SRE-M										
52105600	M 20 x 1,5	13.5	7.5 - 9	4.5 - 6	22 / 22	59.5	6	6	9.0	25
52105610	M 20 x 1,5	13.5	9 - 11	5.5 - 7	22 / 22	59.5	6	7	11.0	25
52105620	M 20 x 1,5	16	11 - 13	7 - 9	24 / 24	64.5	6	9	13.0	25
52105630	M 20 x 1,5	16	11 - 13	8 - 10	24 / 24	64.5	6	10	13.0	25
52105640	M 20 x 1,5	16	13.5 - 15	9 - 11	24 / 24	64.5	6	11	15.0	25
52105650	M 25 x 1,5	21	13.5 - 15	10 - 12	30 / 30	78.0	7	12	15.0	25
52105660	M 25 x 1,5	21	15 - 17	12 - 14	30 / 30	78.0	7	14	17.0	25
52105670	M 25 x 1,5	21	17 - 19	13 - 15	30 / 30	78.0	7	15	19.0	25
52105680	M 25 x 1,5	21	18 - 20	14 - 16	30 / 30	78.0	7	16	20.0	25
52105690	M 32 x 1,5	29	18 - 20	15 - 17	40 / 40	90.0	8	17	20.0	10
52105700	M 32 x 1,5	29	21 - 23	17 - 19	40 / 40	90.0	8	19	23.0	10
52105710	M 40 x 1,5	36	23.5 - 26	20 - 22	50 / 50	108.0	8	22	26.0	5
52105720	M 40 x 1,5	36	27 - 30	22 - 24	50 / 50	108.0	8	24	30.0	5
52105730	M 40 x 1,5	36	30 - 33	26 - 28	50 / 50	108.0	8	28	33.0	5
52105740	M 40 x 1,5	36	32 - 35	28 - 30	50 / 50	108.0	8	30	35.0	5

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16