

SKINDICHT® MINI COLD

SKINDICHT® MINI, cable gland for the smallest conductor sizes and high packing density, gentle cable clamping and high degree of protection

Info

For low temperature ranges up to -60°C



Supplementary automation components from Lapp



Cold-resistant



Space requirement



Robust



Temperature-resistant

Benefits

High degree of protection
For the smallest conductor sizes
Low height
Gentle cable clamping
High packing density

Application range

For use wherever there is limited assembly space.
Sensors
Measurement and control technology

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® MINI COLD

Product features

Suitable for extreme minus temperatures

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Caution:	Recommendation of torque M 6 x 1 1,5 Nm M 8 x 1 3,0 Nm M 10 x 1 6,0 Nm
Material:	Body: Nickel-plated brass Sealing: Silicone
Protection rating:	IP 66 IP 68 - 5 bar
Temperature range:	-60°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® MINI COLD

Article number	Article designation / size	Ø F mm	SW wrench size mm	Overall length C mm	Thread length D mm	Clear opening F (mm)	Pieces / PU
52001877	M 6 x 1	2 - 3	9	19.7	5	3.0	50
52001878	M 8 x 1	3.5 - 5	11	20.5	5	5.5	50
52001879	M 10 x 1	5.5 - 7	14	22.3	5	7.4	50

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

SKINDICHT® MINI COLD

