


SKINDICHT® SR-SV-M

SKINDICHT® SR-SV-M, robust, metric cable gland for high temperatures, seawater-resistant and resistant to oils, acids and chemicals



Mechanical resistance



Optimum strain relief



Temperature-resistant

Benefits

For high temperatures
Resistant to oils, solvents, acids and chemicals
Seawater-resistant
High strain relief
Robust

Application range

Cables for electrical appliances and machinery that are moved under normal use must be protected against excessive bending as required in accordance with VDE 0700-1

Special cable gland with FKM anti-kink sleeve. Our own reinforced acid-resistant FKM receptacle does not show any effects of aging even after an extended period of use at a temperature of +165 °C.

Machine and turbine manufacturing

Power plant engineering

Laboratory

Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

Note

Counter nut to be used: SKINDICHT® SM-M

Last Update (15.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® SR-SV-M

EMC version is available upon request

Example description:

SR-SV-M 20/11/7

20 = metric connection thread

11 = PG function thread

7 = clear opening of seal

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: Cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class-Description: Cable screw gland

Caution:

The installation dimensions
can be found in appendix T21

On request:

Available with long connection thread

Material:

Body: nickel-plated brass

O-ring: FKM

Anti-kink protection: FKM

Protection rating:

IP 65

Temperature range:

-20°C to +165°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® SR-SV-M

Article number	Article designation / size	Clamping range ØF mm	Max. fitting size for installation (mm)	Function thread PG	SW1/SW2 mm	Overall length C mm	Thread length D mm	Clear opening F (mm)	Pieces / PU
SKINDICHT® SR-SV-M									
52105820	M 20 x 1,5	5.5 - 7.0	28	11	22 / 20	56.0	6	7.0	25
52105830	M 20 x 1,5	7.5 - 9.0	28	11	22 / 20	56.0	6	9.0	25
52105840	M 20 x 1,5	7.5 - 9.0	32	13.5	22 / 22	61.5	6	9.0	25
52105850	M 20 x 1,5	8.5 - 11.0	32	13.5	22 / 22	61.5	6	11.0	25
52105860	M 20 x 1,5	10.5 - 13.0	32	13.5	22 / 22	61.5	6	13.0	25
52105870	M 20 x 1,5	11.0 - 13.0	35	16	24 / 24	66.5	6	13.0	10
52105880	M 20 x 1,5	12.0 - 15.0	35	16	24 / 24	66.5	6	15.0	10
52105890	M 25 x 1,5	13.5 - 15.0	40	21	30 / 30	79.0	7	15.0	10
52105900	M 25 x 1,5	15.5 - 17.0	46	21	30 / 30	79.0	7	17.0	10
52105910	M 25 x 1,5	16.5 - 19.0	46	21	30 / 30	79.0	7	19.0	10

Last Update (15.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16