


## SKINDICHT® SR-SV-M

SKINDICHT® SR-SV-M, robust, metric cable gland for high temperatures, seawater-resistant and resistant to oils, acids and chemicals



Mechanical resistance



Optimum strain relief



Temperature-resistant

### Benefits

- For high temperatures
- Resistant to oils, solvents, acids and chemicals
- Seawater-resistant
- High strain relief
- Robust

### Application range

Cables for electrical appliances and machinery that are moved under normal use must be protected against excessive bending as required in accordance with VDE 0700-1

Special cable gland with FKM anti-kink sleeve. Our own reinforced acid-resistant FKM receptacle does not show any effects of aging even after an extended period of use at a temperature of +165 °C.

- Machine and turbine manufacturing
- Power plant engineering
- Laboratory

### Product Make-up

- Metric connection thread acc. to DIN EN 60423
- Basis for technical information DIN IEC 62444

### Note

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SKINDICHT® SR-SV-M

Counter nut to be used: SKINDICHT® SM-M

EMC version is available upon request

Example description:

SR-SV-M 20/11/7

20 = metric connection thread

11 = PG function thread

7 = clear opening of seal

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: Cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class-Description: Cable screw gland

Caution:

The installation dimensions  
can be found in appendix T21

On request:

Available with long connection thread

Material:

Body: nickel-plated brass

O-ring: FKM

Anti-kink protection: FKM

Protection rating:

IP 65

Temperature range:

-20°C to +165°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINDICHT® SR-SV-M**

Article number	Article designation / size	Clamping range ØF mm	Max. fitting size for installation (mm)	Function thread PG	SW1/SW2 mm	Overall length C mm	Thread length D mm	Clear opening F (mm)	Pieces / PU
SKINDICHT® SR-SV-M									
52105820	M 20 x 1,5	5.5 - 7.0	28	11	22 / 20	56.0	6	7.0	25
52105830	M 20 x 1,5	7.5 - 9.0	28	11	22 / 20	56.0	6	9.0	25
52105840	M 20 x 1,5	7.5 - 9.0	32	13.5	22 / 22	61.5	6	9.0	25
52105850	M 20 x 1,5	8.5 - 11.0	32	13.5	22 / 22	61.5	6	11.0	25
52105860	M 20 x 1,5	10.5 - 13.0	32	13.5	22 / 22	61.5	6	13.0	25
52105870	M 20 x 1,5	11.0 - 13.0	35	16	24 / 24	66.5	6	13.0	10
52105880	M 20 x 1,5	12.0 - 15.0	35	16	24 / 24	66.5	6	15.0	10
52105890	M 25 x 1,5	13.5 - 15.0	40	21	30 / 30	79.0	7	15.0	10
52105900	M 25 x 1,5	15.5 - 17.0	46	21	30 / 30	79.0	7	17.0	10
52105910	M 25 x 1,5	16.5 - 19.0	46	21	30 / 30	79.0	7	19.0	10

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16