

SKINTOP® MULTI VENT

SKINTOP® MULTI, bushing system for installation of cables that have not been assembled, high packing density, large variable clamping ranges

Info

Compact multi cable bushing system with innovative gel technology
Breathable pressure compensation element with membrane technology



Supplementary automation components from Lapp



Mechanical and plant engineering



Wide clamping range



Halogen-free



Assembly time



Optimum strain relief



Space requirement



UV-resistant

Benefits

Large clamping range of 4 mm and AS-I BUS entry system by elastic gel technology with innovative membrane technology
Easy installation of the cables even for high packing density
Optimum strain relief at the entire cable bundle

Last Update (06.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® MULTI VENT

Error reduction through clear assignment of cable to be installed by a clear marker of implementing points
Not used bushings remain securely sealed

Application range

Used in areas where a lot of cables and wires need to be inserted into housings with minimum space requirements
For not harnessed cables and media hoses
Apparatus and switch cabinet construction
Automation technology

Product features

Special integrated membrane equalize the pressure balance and enables humidity to stay out of the junction box
Integrated seal for the cable & housing (captive)
Halogen-free
UV-, ozone- and oil-resistant
The adhesive gel provides a very easy positioning at the enclosure during the assembling

Product Make-up

For cut-outs for 24-pin industrial connectors (36 x 112 mm)

Note

Air flow rates: 0.65 l/min

Included

SKINTOP® MULTI VENT including mounting material

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000240 ETIM 5.0 Class-Description: Cable entry
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000240 ETIM 6.0 Class-Description: Cable entry
Note:	Individual hole configuration on request
Material:	Frame: Polycarbonat Sealing: Gel Pressure compensation unit: PBT, PTFE, NBR
Protection rating:	IP 68
Temperature range:	-30°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINTOP® MULTI VENT

Article number	Article designation / size	Max. number of executions	Number of cables x cable Ø	Pieces / PU
52220092	SKINTOP® MULTI VENT Version 1	21	6 x 8-12 mm, 15 x 3-7 mm	1
52220093	SKINTOP® MULTI VENT Version 2	20	4 x 2-6 mm, 8 x 4-8 mm, 3 x 5-9 mm, 2 x 8-12 mm, 1 x 12-16 mm, 2 x AS-I BUS / 2 x 2-4 mm	1
52220094	SKINTOP® MULTI VENT Version 3	29	29 x 2-6 mm	1
52220095	SKINTOP® MULTI VENT Version 4	11	8 x 8-12 mm, 2 x 12-16 mm, 1 x 16-20 mm	1

Last Update (06.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

SKINTOP® MULTI VENT



Last Update (06.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16