SKINTOP® CUBE MULTI

SKINTOP® CUBE MULTI, cable bushing system for installation of not harnessed cables, high packing density, large, variable clamping ranges

Info

Push the cable through the gel membrane and connect directly
Huge potential of savings through quick installation







Supplementary automation components from Lapp

Mechanical and plant engineering

Wide clamping range

Assembly time

Optimum strain relief

Benefits

Large, variable clamping ranges due to elastic gel technology
Easy installation of the cables even for high packing density
Optimum strain relief at the entire cable bundle
Simplified servicing due to easy assembling and disassembling
Not used bushings remain securely sealed

Application range

Used in areas where a lot of cables and wires need to be inserted into housings with minimum space requirements
For not harnessed cables and media hoses
Apparatus and switch cabinet construction
Automation technology

Last Update (26.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

SKINTOP® CUBE MULTI

Product features

SKINTOP® CUBE MULTI Version 1
Number of cable bushings:
9 x 3-6 mm clamping range
9 x 6-9 mm clamping range
2 x 9-13 mm clamping range
1 x 13-16 mm clamping range
SKINTOP® CUBE MULTI Version 2
Number of cable bushings:
23 x 5-8 mm clamping range

Norm references / Approvals

UL 50, UL 50E, CSA C22.2
UL 508A for Industrial Control Panels
UL File No. E349737

Product Make-up

The system consists of SKINTOP® CUBE FRAME and a gel insert SKINTOP® CUBE MULTI.
Removal of the gel insert by opening the holder
For cut-outs for 24-pin industrial connectors (36 x 112 mm)

Note

For better strain relief, the cable bundle can be fixed with help of a cable tie

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000240 ETIM 5.0 Class-Description: Cable entry
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000240 ETIM 6.0 Class-Description: Cable entry
Certifications:	UL File No. E349737 Fire behaviour according to UL94 V-2
Note:	Individual hole configuration on request
Material:	Frame: Glass fiber reinforced polyamide Frame seal: CR Gel insert: PC / Gel
Protection rating:	IP 66
Temperature range:	-30 °C to +100 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2024 Lapp Group - Technical changes reserved

LAPP

SKINTOP® CUBE MULTI

PRODUCT INFORMATION

Article number	Article designation / size	Max. number of executions	Number of cables x clamping range
SKINTOP® CUBE MULTI Gel-insert			
52220050	SKINTOP® CUBE MULTI Version 1	21	9 x 3-6 mm; 9 x 6-9 mm; 2 x 9-13 mm; 1 x 13-16 mm
52220053	SKINTOP® CUBE MULTI Version 2	23	23 x 5-8 mm
SKINTOP® CUBE MULTI Gel-insert incl. frame			
52220056	SKINTOP® CUBE MULTI Version 1 incl. frame	21	9 x 3-6 mm; 9 x 6-9 mm; 2 x 9-13 mm; 1 x 13-16 mm
52220057	SKINTOP® CUBE MULTI Version 2 incl. frame	23	23 x 5-8 mm
SKINTOP® CUBE Frame			
52220001	SKINTOP® CUBE FRAME 24	-	-

Last Update (26.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

SKINTOP® CUBE MULTI



Last Update (26.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16