

SKINTOP® MULTI

SKINTOP® MULTI, bushing system for installation of cables that have not been assembled, high packing density, large variable clamping ranges

Info

Compact multi cable bushing system with innovative gel technology



Supplementary automation components from Lapp



Mechanical and plant engineering



Wide clamping range



Halogen-free



Assembly time



Optimum strain relief



Space requirement



UV-resistant

Benefits

Large clamping range of 4 mm and AS-I BUS entry system by elastic gel technology with innovative membrane technology

Easy installation of the cables even for high packing density

Optimum strain relief at the entire cable bundle

Error reduction through clear assignment of cable to be installed by a clear marker of implementing points

Last Update (16.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® MULTI

Not used bushings remain securely sealed

Application range

Used in areas where a lot of cables and wires need to be inserted into housings with minimum space requirements
For not harnessed cables and media hoses
Apparatus and switch cabinet construction
Automation technology

Product features

Cables can be inserted directly without using a pricking awl
Integrated seal for the cable & housing (captive)
Halogen-free and silicone-free
UV-, ozone- and oil-resistant
The adhesive gel provides a very easy positioning at the enclosure during the assembling

Norm references / Approvals

UL 50, UL 50E, CSA C22.2
UL 508A for Industrial Control Panels
UL File No. E349737

Product Make-up

For cut-outs for 24-pin industrial connectors (36 x 112 mm)

Included

SKINTOP® MULTI including mounting material

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000240 ETIM 5.0 Class-Description: Cable entry
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000240 ETIM 6.0 Class-Description: Cable entry
Certifications:	UL File No. E349737 Fire behaviour acc. to UL94 V-2 Hazard Level HL 2 acc. to EN 45545-2
Note:	Individual hole configuration on request
Material:	Frame: Polycarbonat Sealing: Gel
Protection rating:	IP 68
Temperature range:	-30°C to +110°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINTOP® MULTI

Article number	Article designation / size	Max. number of executions	Number of cables x cable Ø	Pieces / PU
52220065	SKINTOP® MULTI Version 1	22	16 x 3-7 mm, 6 x 8-12 mm	1
52220073	SKINTOP® MULTI Version 2	21	5 x 2-6 mm, 8 x 4-8 mm, 3 x 5-9 mm, 2 x 8-12 mm, 1 x 12-16 mm, 2 x AS-I BUS / 2 x 2-4 mm	1
52220080	SKINTOP® MULTI Version 3	30	30 x 2-6 mm	1
52220085	SKINTOP® MULTI Version 4	11	8 x 8-12 mm, 2 x 12-16 mm, 1 x 16-20 mm	1
52220101	SKINTOP® MULTI Version 5	27	27 x 4-8 mm	1
52220104	SKINTOP® MULTI Version 6	24	10 x 2-6 mm, 8 x 4-8 mm, 4 x 7-11mm, 2 x 10-14mm	1

Last Update (16.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® MULTI

