

SKINTOP® DIX-M AUTOMATION

SKINTOP® DIX-M AUTOMATION, multiple sealing insert for optimal sealing when using pre-assembled cables

Info

New versions of the slotted sealing inserts cover pre-assembled cables with an outside diameter of 3-10 mm



Supplementary automation components from Lapp



Assembly time



Optimum strain relief



Temperature-resistant



UV-resistant

Benefits

Optimal seal when using AS-I bus cables

Easy insertion of pre-assembled cables (with fieldbus or RJ-45 connector) by slotted sealing

Optimum strain relief

Application range

For use in SKINTOP® cable glands

Can be used instead of the inner sealing insert

Control cabinets

Control panels

Automation technology

Product Make-up

Precise cut for AS-I bus cables

Seal with hole and cut for easy insertion of pre-assembled field bus cables

Technical Data

Last Update (28.10.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® DIX-M AUTOMATION

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000032 ETIM 5.0 Class-Description: Plug for cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000032 ETIM 6.0 Class-Description: Plug for cable screw gland
On request:	Special shapes
Colour delivered:	Black, RAL 9005
Material:	NBR
Protection rating:	IP 54 IP 66 and IP 68 - 5 bar, 30 min (only applies to slotted DIX inserts if the specified clamping range is observed)
Temperature range:	-40°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINTOP® DIX-M AUTOMATION

Article number	Article designation / size	Number of cables x cable Ø (mm)	Pieces / PU
SKINTOP® DIX-M ASI			
53611001	M 20	1	50
SKINTOP® DIX-M ASI DUO			
53611004	M 25	2	50
SKINTOP® DIX-M CUT			
53440982	M 25	1 x 3.0 - 7.0	50
53440983	M 25	1 x 4.0 - 9.0	50
53440970	M 32	1 x 4.5 - 6.5	50
53310444	M 40	3 x 7.0 - 10.0	25

Last Update (28.10.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16