


SKINTOP® COLD-R

SKINTOP® COLD-R, metric brass cable gland, high cold-resistance and cold impact resistance, with reducing seal insert

Info

For extreme sub-zero temperatures



Good chemical resistance



Cold-resistant



Corrosion-resistant



Mechanical resistance



Temperature-resistant

Benefits

High cold-resistance

Cold impact resistance

High mechanical stability

Optimum strain relief

Wide, variable clamping ranges

Application range

With reducing seal insert, to seal cables with smaller outer diameters

Norm references / Approvals

UL File Nr. E79903

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® COLD-R

Product Make-up

Metric connection thread acc. to DIN EN 60423
Basis for technical information DIN IEC 62444

Technical Data

| | |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland |
| Caution: | Refer to Appendix T21 for the installation dimensions and torques |
| Material: | Body: nickel-plated brass Insert: special polyamide Sealing ring: silicone O-ring: silicone |
| Protection rating: | IP 68 - 10 bar (M12 - M20) IP 68 - 5 bar (M25 - M63) NEMA Type 1, 2, 4x, 6, 12 |
| Temperature range: | -70°C to +100°C |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINTOP® COLD-R

| Article number | Article designation / size | Ø F mm | SW wrench size mm | Overall length C mm | Thread length D mm | Pieces / PU |
|-----------------|----------------------------|---------|-------------------|---------------------|--------------------|-------------|
| SKINTOP® COLD-R | | | | | | |
| 53113600 | M 12 x 1,5 | 1 - 5 | 16 | 26.5 | 6.5 | 100 |
| 53113610 | M 16 x 1,5 | 2 - 7 | 20 | 33.0 | 7 | 100 |
| 53113620 | M 20 x 1,5 | 5 - 10 | 24 | 37.0 | 8 | 50 |
| 53113630 | M 25 x 1,5 | 6 - 13 | 29 | 38.5 | 8 | 25 |
| 53113640 | M 32 x 1,5 | 7 - 15 | 36 | 45.5 | 9 | 25 |
| 53113650 | M 40 x 1,5 | 15 - 23 | 45 | 48.0 | 9 | 10 |
| 53113660 | M 50 x 1,5 | 22 - 29 | 54 | 55.5 | 10 | 5 |
| 53113670 | M 63 x 1,5 | 28 - 39 | 67 | 67.0 | 15 | 5 |

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16