



## SKINTOP® INOX SC NPT

SKINTOP® INOX / SKINTOP® INOX-R, corrosion-resistant stainless steel cable gland with smooth surfaces, compact design, sea water-resistant

### Info

Stainless steel version with compact design  
Optimum EMC protection



Food & Beverage



Suitable for outdoor use



Good chemical resistance



Wide clamping range



Halogen-free



Mechanical resistance



Interference signals



Temperature-resistant

### Benefits

Smooth surfaces - no edges  
Compact design

Last Update (24.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SKINTOP® INOX SC NPT

Wide, variable clamping ranges  
Low-resistance screen contact, optimum EMC protection  
Highly conductive, flexible EMC contact for clamping various screen diameters

### Application range

For EMC-compliant earthing of the copper braiding  
Pharmaceutical industry  
Food industry (product-free zone, splash zone)  
Onshore and offshore applications  
Bottling plants and breweries

### Norm references / Approvals

ECOLAB®  
Industry standard in the field of professional cleaning and disinfection in the food and beverage industry  
DIN EN 1672-2  
Guideline for the design of machinery  
DIN EN ISO 14159  
Security of machinery – Hygienic requirements for the design of machinery  
NSF/ANSI 169  
Hygienic design for machinery and components

### Product Make-up

NPT connection thread acc. to ASME B1.20.1 - 2013

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Material:	Body: stainless steel V4A (1.4404 / 316L) Insert: polyamide Sealing: silicone O-Ring: silicone Halogen-free
Protection rating:	NEMA Type 1, Type 2, Type 4X, Type 6, Type 12 according to UL50E IP 68 - 5 bar
Temperature range:	-40 °C to +100 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINTOP® INOX SC NPT**

Article number	Article designation / size	Ø F mm	SW wrench size mm	Overall length C mm	Thread length D mm	Pieces / PU
53806818	NPT 1/4"	4 - 7	16	37.8	15	5
53806819	NPT 3/8"	6 - 10	20	40.4	15	5
53806820	NPT 1/2"	7 - 13	24	42.5	15	5
53806821	NPT 3/4"	9 - 17	29	46.2	15	5
53806822	NPT 1"	11 - 21	36	50.6	15	5
53806823	NPT 1 1/4"	19 - 28	45	59.2	17	5
53806824	NPT 1 1/2"	27 - 35	54	63.2	17	5

Last Update (24.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16