

SKINTOP® ST-HF-M

Halogen-free plastic cable gland

SKINTOP® ST-HF-M, halogen-free, metric plastic cable gland, extremely flame-retardant and self-extinguishing, maximum reliability

Info

Cable gland for railway applications

Hazard Level: HL 3



Rail



Good chemical resistance



Flame-retardant



Wide clamping range



Halogen-free



Variety of approval certifications

Benefits

Maximum reliability

Extremely flame-retardant according to UL 94 V0

Completely halogen-free (including sealing material)

Self-extinguishing, no dripping

Permanent vibration protection

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® ST-HF-M

Application range

Underground railways and trains
When the protection of people and property is a priority
Public buildings
Ventilation systems
Tunnel construction

Norm references / Approvals

DIN EN 45545-2 (HL3)
Filament testing according to EN 60695-2-1/1 +960 °C

Product Make-up

Metric connection thread acc. to DIN EN 60423
Basis for technical information DIN IEC 62444

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Caution:	Refer to Appendix T21 for the installation dimensions and torques
Colour delivered:	RAL 7035 light grey Black (RAL 9005), UV-resistant
Material:	Body: polyamide Sealing ring: special elastomer O-ring: special elastomer
Protection rating:	IP 68 - 5 bar
Temperature range:	Fixed: -40 °C to +100 °C Dynamic: -20 °C to +100 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINTOP® ST-HF-M

Article number	Article designation / size	Ø F mm	SW wrench size mm	Overall length C mm	Thread length D mm	Pieces / PU
SKINTOP® ST-HF-M light grey						
53111407	M 12 x 1,5	4 - 5.5	15	30.0	8	100
53111417	M 16 x 1,5	4.5 - 9	19	34.0	8	100
53111427	M 20 x 1,5	7 - 13	25	37.0	9	100
53111437	M 25 x 1,5	9 - 17	30	40.0	10	50
53111447	M 32 x 1,5	11 - 21	36	47.0	10	25
53111457	M 40 x 1,5	19 - 28	46	52.0	10	10
53111467	M 50 x 1,5	27 - 35	55	62.0	12	5
53111477	M 63 x 1,5	34 - 45	66	71.0	12	5
SKINTOP® ST-HF-M black						
53111408	M 12 x 1,5	4 - 5.5	15	30.0	8	100
53111418	M 16 x 1,5	4.5 - 9	19	34.0	8	100
53111422	M 20 x 1,5	7 - 13	25	37.0	9	100
53111438	M 25 x 1,5	9 - 17	30	40.0	10	50
53111448	M 32 x 1,5	11 - 21	36	47.0	10	25
53111458	M 40 x 1,5	19 - 28	46	52.0	10	10
53111468	M 50 x 1,5	27 - 35	55	62.0	12	5
53111478	M 63 x 1,5	34 - 45	66	70.0	12	5

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16