


## SKINTOP® FIBER

SKINTOP® FIBER, cable gland for fiber optic cables, strain relief and sealing

### Info

Enables a good fixation and sealing without impairing the transmission performance



Assembly time

### Benefits

- Special sealing insert with 12 x 0-3mm clamping range
- Easy assembly and disassembly thanks to the insertion aid
- Smooth clamping of sensitive fibre optic cables due to the soft EPDM material
- The slotted holes allow the insertion of pre-assembled fiber optical cables

### Application range

- Assembly of fiber optic cables
- Broadband expansion
- FTTx applications
- Industry 4.0 applications
- Suitable for indoor and outdoor use

### Product Make-up

- Metric connection thread acc. to DIN EN 60423
- Basis for technical information DIN IEC 62444

### Note

To achieve a high degree of protection, unoccupied holes can be closed with a SKINTOP DIX-DV plug

### Included

Counter nut SKINTOP® GMP-GL-M included

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SKINTOP® FIBER

### Technical Data

Caution:	Tightening torques see installation instructions
Colour delivered:	RAL 7035 light grey
Material:	Body: Polyamide Seal: EPDM
Protection rating:	IP 66 (when all boreholes are optimally occupied)
Temperature range:	-20°C to +120°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINTOP® FIBER**

Article number	Article designation / size	Ø F mm	SW wrench size mm	Overall length C mm	Thread length D mm	Pieces / PU
54113180	M 32 x 1,5	0 - 3	36	47.0	10	10

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16