

## SKINTOP® GMP-HF-M

SKINTOP® GMP-HF-M, halogen-free counter nuts, extremely flame-retardant, self-extinguishing, no dripping, for public buildings



Halogen-free



Assembly time



Temperature-resistant



Variety of approval certifications

### Benefits

Halogen-free

Extremely flame-retardant according to UL 94 V0

Self-extinguishing, no dripping

### Application range

For locking SKINTOP® cable glands in boreholes without thread.

Airports

Tunnel construction

Underground railways

Public buildings

### Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

### Note

Designed for use with SKINTOP® ST-HF-M

Last Update (17.09.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SKINTOP® GMP-HF-M

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Colour delivered:	Light grey (RAL 7035)
Material:	halogenfree polyamide acc. to UL 94 V0
Temperature range:	Fixed: -40°C to +100°C Dynamic: -20°C to +100°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINTOP® GMP-HF-M**

Article number	Article designation / size	SW wrench size mm	PU
SKINTOP® GMP-HF-M			
53119200	M 12 x 1,5	17	100
53119210	M 16 x 1,5	22	100
53119220	M 20 x 1,5	27	100
53119230	M 25 x 1,5	34	100
53119240	M 32 x 1,5	41	100
53119205	-	-	-
53119215	-	-	-
53119225	-	-	-
53119235	-	-	-
53119245	-	-	-
53119255	-	-	-
53119250	M 40 x 1,5	50	25
53119265	-	-	-
53119260	M 50 x 1,5	60	25
53119275	-	-	-
53119270	M 63 x 1,5	75	25

Last Update (17.09.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03.16