ETHERLINE® ACCESS PNF


Industrial PROFINET® Switches in compact design

Industrial network switches for ethernet based solutions in Smart Factories.

Info
compact design
compatible for PROFINET® networks







Supplementary automation components from Lapp

Mechanical and plant engineering

Benefits
compact design with high port density
easy Configuration via web-interface
space saving and industrial grade DIN rail mounting

Application range
industrial application
PROFINET®-networks

Product features
PROFINET® switches with 4, 8 and 16 ports
PROFINET® Conformance Class B
Prioritization of PROFINET® telegramms
Neighbourhood detection LLDP
RJ45 Ports: 10/100/1000 BaseT(X)

Norm references / Approvals
UL 61010

Last Update (24.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

ETHERLINE® ACCESS PNF

Technical Data

power supply:	DC 24 V (18-30 V DC)
Protection rating:	IP20
Temperature range:	-40 °C up to +75 °C

Note

PROFINET® is a registered trademark of the PNO (PROFIBUS user organisation)
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (24.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

LAPP

ETHERLINE® ACCESS PNF

PRODUCT INFORMATION

Article number	Article designation	Type	number of ports	Feature	MTBF in years
21700140	ETHERLINE® ACCESS PNF04T	Managed	4 x RJ45	dla sieci Profinet	>15.21
21700142	ETHERLINE® ACCESS PNF08T	Managed	8 x RJ45	-	>13.09
21700143	ETHERLINE® ACCESS PNF16T	Managed	16 x RJ45	-	>9.64

©2023 Lapp Group - Technical changes reserved