

ETHERLINE® Cat.6A Flex patch cables

Pre-assembled patch cables based on our ETHERLINE® Cat.7 FLEX.

ETHERLINE® Cat.6A Flex patch cables

Info

Additional variants are available at
www.lappgroup.com/assemblyfinder
or on request.
Based on 2170934



Supplementary automation components from Lapp



Mechanical and plant engineering



Flame-retardant



Halogen-free



Assembly time



Interference signals

Benefits

Only for patch cable applications
(max. 60 m)
Plug & Play for flexible connection solutions

Application range

CAT.6A qualified for 10Gbit/s
M12 X-coded connectors, comp. with IEC 61076-2-109
RJ45 connectors, comp. with IEC 60603-7-51

Product features

Meets the requirements according to CAT.6A, ISO/IEC 11801 and EN 50173
4pair: 10/100/1000 Mbit/s for Industrial Ethernet

Product Make-up

Braided conductor, 4x2x AWG26/7
Twisted pair construction permits largely interference-free operation (decoupling).

Last Update (07.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ETHERLINE® Cat.6A Flex patch cables

High-quality, double screening ensures high transmission reliability in areas with electromagnetic interference

Outer sheath: PUR compound, halogen-free

Pre-assembled patchcord with norm-compliant connectors

Colour: green (based on RAL 6018)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC002599 ETIM 5.0 Class-Description: Patch cord copper (twisted pair) industry
Minimum bending radius:	Fixed installation: 4 x outer diameter Flexing: up from 10 x outer diameter
Protection rating:	M12 -IP67 RJ45 - IP20
Coding:	M12: X-Standard
Temperature range:	Flexing: -30°C to +80°C (M12) Flexing: -40°C to +70°C (RJ45)

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ETHERLINE® Cat.6A Flex patch cables

Article number	Article designation	Length (m)	Copper index (kg/km)
M12 (X-coded), plug to M12 (X-coded), plug			
2172326	IE-6A-M12X-S-0,5-P-4-26-7-M12X-S	0.5	14
2172327	IE-6A-M12X-S-1-P-4-26-7-M12X-S	1	28
2172328	IE-6A-M12X-S-2-P-4-26-7-M12X-S	2	56
2172329	IE-6A-M12X-S-3-P-4-26-7-M12X-S	3	84
2172330	IE-6A-M12X-S-5-P-4-26-7-M12X-S	5	140
2172332	IE-6A-M12X-S-10-P-4-26-7-M12X-S	10	280
2172334	IE-6A-M12X-S-20-P-4-26-7-M12X-S	20	560
M12 (X-coded), plug to M12 (X-coded), flange-socket			
2172335	IE-6A-M12X-S-0,5-P-4-26-7-M12XF-S	0.5	14
2172336	IE-6A-M12X-S-1-P-4-26-7-M12XF-S	1	28
2172337	IE-6A-M12X-S-2-P-4-26-7-M12XF-S	2	56
2172338	IE-6A-M12X-S-3-P-4-26-7-M12XF-S	3	84
2172339	IE-6A-M12X-S-5-P-4-26-7-M12XF-S	5	140
2172341	IE-6A-M12X-S-10-P-4-26-7-M12XF-S	10	280
2172343	IE-6A-M12X-S-20-P-4-26-7-M12XF-S	20	560
M12 (X-coded), flange-socket to M12 (X-coded), flange-socket			
2172344	IE-6A-M12XF-S-0,5-P-4-26-7-M12XF-S	0.5	14
2172345	IE-6A-M12XF-S-1-P-4-26-7-M12XF-S	1	28
2172346	IE-6A-M12XF-S-2-P-4-26-7-M12XF-S	2	56
2172347	IE-6A-M12XF-S-3-P-4-26-7-M12XF-S	3	84
2172348	IE-6A-M12XF-S-5-P-4-26-7-M12XF-S	5	140
2172350	IE-6A-M12XF-S-10-P-4-26-7-M12XF-S	10	280
2172352	IE-6A-M12XF-S-20-P-4-26-7-M12XF-S	20	560
M12 (X-coded), plug to RJ45, plug			
2172380	IE-6A-M12X-S-0,5-P-4-26-7-RJ45	0.5	14
2172381	IE-6A-M12X-S-1-P-4-26-7-RJ45	1	28
2172382	IE-6A-M12X-S-2-P-4-26-7-RJ45	2	56
2172383	IE-6A-M12X-S-3-P-4-26-7-RJ45	3	84
2172384	IE-6A-M12X-S-5-P-4-26-7-RJ45	5	140
2172386	IE-6A-M12X-S-10-P-4-26-7-RJ45	10	280
2172388	IE-6A-M12X-S-20-P-4-26-7-RJ45	20	560
M12 (X-coded), flange-socket to RJ45, plug			
2172389	IE-6A-M12XF-S-0,5-P-4-26-7-RJ45	0.5	14
2172390	IE-6A-M12XF-S-1-P-4-26-7-RJ45	1	28

Last Update (07.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

ETHERLINE® Cat.6A Flex patch cables

Article number	Article designation	Length (m)	Copper index (kg/km)
2172391	IE-6A-M12XF-S-2-P-4-26-7-RJ45	2	56
2172392	IE-6A-M12XF-S-3-P-4-26-7-RJ45	3	84
2172393	IE-6A-M12XF-S-5-P-4-26-7-RJ45	5	140
2172395	IE-6A-M12XF-S-10-P-4-26-7-RJ45	10	280
2172397	IE-6A-M12XF-S-20-P-4-26-7-RJ45	20	560
RJ45, plug to RJ45, plug			
2172362	IE-6A-RJ45-0,5-P-4-26-7-RJ45	0.5	14
2172363	IE-6A-RJ45-1-P-4-26-7-RJ45	1	28
2172364	IE-6A-RJ45-2-P-4-26-7-RJ45	2	56
2172365	IE-6A-RJ45-3-P-4-26-7-RJ45	3	84
2172366	IE-6A-RJ45-5-P-4-26-7-RJ45	5	140
2172368	IE-6A-RJ45-10-P-4-26-7-RJ45	10	280
2172370	IE-6A-RJ45-20-P-4-26-7-RJ45	20	560
M12 (X-coded), plug to open end			
2172317	IE-6A-M12X-S-0,5-P-4-26-7-OE	0.5	14
2172318	IE-6A-M12X-S-1-P-4-26-7-OE	1	28
2172319	IE-6A-M12X-S-2-P-4-26-7-OE	2	56
2172320	IE-6A-M12X-S-3-P-4-26-7-OE	3	84
2172321	IE-6A-M12X-S-5-P-4-26-7-OE	5	140
2172323	IE-6A-M12X-S-10-P-4-26-7-OE	10	280
2172325	IE-6A-M12X-S-20-P-4-26-7-OE	20	560
M12 (X-coded), flange-socket to open end			
2172353	IE-6A-M12XF-S-0,5-P-4-26-7-OE	0.5	14
2172354	IE-6A-M12XF-S-1-P-4-26-7-OE	1	28
2172355	IE-6A-M12XF-S-2-P-4-26-7-OE	2	56
2172356	IE-6A-M12XF-S-3-P-4-26-7-OE	3	84
2172357	IE-6A-M12XF-S-5-P-4-26-7-OE	5	140
2172359	IE-6A-M12XF-S-10-P-4-26-7-OE	10	280
2172361	IE-6A-M12XF-S-20-P-4-26-7-OE	20	560
RJ45, plug to open end			
2172371	IE-6A-RJ45-0,5-P-4-26-7-OE	0.5	14
2172372	IE-6A-RJ45-1-P-4-26-7-OE	1	28
2172373	IE-6A-RJ45-2-P-4-26-7-OE	2	56
2172374	IE-6A-RJ45-3-P-4-26-7-OE	3	84
2172375	IE-6A-RJ45-5-P-4-26-7-OE	5	140

Last Update (07.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03_16

ETHERLINE® Cat.6A Flex patch cables

Article number	Article designation	Length (m)	Copper index (kg/km)
2172377	IE-6A-RJ45-10-P-4-26-7-OE	10	280
2172379	IE-6A-RJ45-20-P-4-26-7-OE	20	560

Last Update (07.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16