

ETHERLINE® FIRE

Industrial Ethernet cable with insulation integrity

Industrial Ethernet cable for fixed installation, insulation integrity for 120 minutes, qualified for 1 GBit/s

Info

insulation integrity for at least 120 minutes in the event of fire



Flame-retardant



Halogen-free



Reliability



Interference signals

Benefits

Ensures that the cable can still transmit data during and after a fire for 120 min (according to EN50200)

High-quality, double screening ensures high transmission reliability in areas with electromagnetic interference

Application range

In industrial areas that use fire as a tool
Highly combustible or fire-prone areas
for fixed installation
For indoor use

Product features

Fire behaviour:

- Halogen-free (IEC 60754-1 & EN50267-2-1)
- Flame-retardant (IEC 60332-1)
- Fire retardant (IEC 60332-3-24)
- Low smoke density (IEC 61034-2)

Circuit integrity for data cables PH120 (120 minutes) acc. to EN 50289-4-16

Last Update (13.05.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ETHERLINE® FIRE

Product Make-up

Solid bare copper conductor

Core insulation: Based on Polyolefin

each insulation will be wrapped with a special tape (anti-fire barrier)

Twisting: 2 twisted-pair cores, stranding from 4 pairs

Halogen-free and flame-retardant FRNC outer sheath, colour: red (similar to RAL3000)

Technical Data

Classification ETIM 5:	ETIM 5.0/6.0 Class-ID: EC000830 ETIM 5.0/6.0 Class-Description: Data cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000830 ETIM 6.0 Class-Description: Data cable
Peak operating voltage:	(not for power applications) 125 V
Minimum bending radius:	Fixed installation: 15 x outer diameter
Characteristic impedance:	nom. 100 Ω acc. to IEC 61156-5
Temperature range:	Fixed installation: -20 °C to +70 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Detailed data sheets are available upon request. Please specify the type/dimensions of the required cable.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.



ETHERLINE® FIRE

Article number	Article designation	Number of pairs and AWG per conductor	Core diameter in mm	Outer diameter mm	Copper index (kg/km)	Weight (kg/km)
2170913	ETHERLINE® FIRE Cat.6 PH120	4 x 2 x AWG22/1	1.5	10.2	48	145
2170905	ETHERLINE® FIRE Cat.5e PH120	4 x 2 x AWG23/1	0.95	8.6	24	75

Last Update (13.05.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

ETHERLINE® FIRE

