

ETHERLINE® PN FD Cat.5 RJ45

PROFINET Patchcord RJ45

Industrial Ethernet Patchcord, Profinet Type C, Cat.5, plug RJ45, PUR, for drag chain

Info

Based on 2170894

Additional variants are available at
www.lappgroup.com/assemblyfinder
or on request.



Supplementary automation components from Lapp



Mechanical and plant engineering



Halogen-free



Mechanical resistance



Assembly time



Power chain



Interference signals

Benefits

Non-permanent connections allow for easy change of equipment
For directly connecting two electric components

Last Update (22.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ETHERLINE® PN FD Cat.5 RJ45

Application range

Highly flexible application
suitable for EtherCAT and EtherNet/IP applications
Suitable for use in industrial applications
For indoor use

Product features

Meets the requirements according to Cat. 5e and class D
2pair: 10/100 Mbit/s for Industrial Ethernet

Norm references / Approvals

The cable is UL/CSA-certified (CMX)

Product Make-up

Braided conductor, 2x2x AWG22/7
Star quad
Overall screening with copper braid and plastic-laminated aluminium foil
Outer sheath made of PUR
Colour: green (based on RAL 6018)
pre-assembled patchcord with RJ45 connectors

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC002599 ETIM 5.0 Class-Description: Patch cord copper (twisted pair) industry
Classification ETIM 6:	ETIM 6.0 Class-ID: EC002599 ETIM 6.0 Class-Description: Patch cord copper (twisted pair) industry
Minimum bending radius:	Flexing: 8 x outer diameter
Protection rating:	RJ45 - IP20
Temperature range:	During installation: -20 °C to +60 °C Fixed installation: -30 °C to +70 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Other lengths and types of connectors are available upon request.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

For detailed technical information please refer to the data sheet

ETHERLINE® PN FD Cat.5 RJ45

Article number	Article designation	Length (m)	Copper index kg/1.000 pieces
straight plug RJ45 on straight plug RJ45			
2171278	IE-PNC-5-RJ45-0,5-P-2-22-FD-RJ45	0.5	15.65
2171279	IE-PNC-5-RJ45-1-P-2-22-FD-RJ45	1	31.3
2171280	IE-PNC-5-RJ45-2-P-2-22-FD-RJ45	2	62.6
2171281	IE-PNC-5-RJ45-3-P-2-22-FD-RJ45	3	93.9
2171282	IE-PNC-5-RJ45-5-P-2-22-FD-RJ45	5	156.5
2171283	IE-PNC-5-RJ45-10-P-2-22-FD-RJ45	10	313
2171284	IE-PNC-5-RJ45-20-P-2-22-FD-RJ45	20	626
straight plug RJ45 on free conductor end			
2171285	IE-PNC-5-RJ45-0,5-P-2-22-FD-OE	0.5	15.65
2171286	IE-PNC-5-RJ45-1-P-2-22-FD-OE	1	31.3
2171287	IE-PNC-5-RJ45-2-P-2-22-FD-OE	2	62.6
2171288	IE-PNC-5-RJ45-3-P-2-22-FD-OE	3	93.9
2171289	IE-PNC-5-RJ45-5-P-2-22-FD-OE	5	156.5
2171290	IE-PNC-5-RJ45-10-P-2-22-FD-OE	10	313
2171291	IE-PNC-5-RJ45-20-P-2-22-FD-OE	20	626