

ETHERLINE® FD CAT.6A

Ethernet cable Category 6_A, Class EA for highly flexible use - verified up to 500 MHz

Industrial Ethernet cable Cat.6A for highflexible use in drag chain, 4 pairs, PVC or PUR outer sheath with UL-approval, 4x2xAWG24/7

Info

CAT.6A for drag chain, qualified for 10Gbit/s
For PROFINET applications with 4 pairs



- Supplementary automation components from Lapp
- Mechanical and plant engineering
- Wind Energy
- Mechanical resistance
- Power chain
- Robust
- Interference signals
- UV-resistant

Benefits

For use in power chains and moving machinery parts in dry or damp rooms

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ETHERLINE® FD CAT.6A

4pair: 100Mbit/s up to 10 Gbit/s for Industrial Ethernet
Premium screening against electromagnetic interference
Can be used for Industrial Ethernet in harsh industrial environments

Application range

For highly flexible applications
(e.g. power chains)
Wiring of machines, tools, devices, appliances and control cabinets
suitable for EtherCAT and EtherNet/IP applications

Product features

PUR version is halogen-free according to VDE 0472-815
Oil-resistant acc. IEC 60811-2-1
CAT.6A for drag chain, qualified for 10Gbit/s
Meets the requirements according to CAT.6A, ISO/IEC 11801 and EN 50173
min. 2.5 million bending cycles in the power chain

Norm references / Approvals

electrical requirements acc. to IEC 61156-6
PUR cable is UL/CSA-certified (CMX)
PUR versions: UL AWM Style 21576
PVC cable is UL/CSA-certified (CM)
Flame retardant acc. to IEC 60332-1-2

Product Make-up

7-wire tinned stranded copper conductor
Core insulation: Based on Polyolefin
S/FTP: copper braid as overall screening and pair screening with aluminium compound foil
Outer sheath: PUR/PVC
Colour: green (based on RAL 6018)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000830 ETIM 5.0 Class-Description: Data cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000830 ETIM 6.0 Class-Description: Data cable
Minimum bending radius:	Fixed installation: 8 x outer diameter Flexing: 15 x outer diameter
Characteristic impedance:	nom. 100 Ω acc. to IEC 61156-6
Temperature range:	Cable with PUR jacket Fixed installation: -40 °C to +80 °C Flexing: -30 °C to +70 °C Cable with PVC jacket Fixed installation: -40 °C to +80 °C Flexing: -10 °C bis +70 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

PROFINET® is a registered trademark of the PNO (PROFIBUS user organisation)

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ETHERLINE® FD CAT.6A

Detailed data sheets are available upon request. Please specify the type/dimensions of the required cable.
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.
UL certifications can be found in the data sheet.

ETHERLINE® FD CAT.6A

Article number	Article designation	Number of pairs and AWG per conductor	Core diameter in mm	Outer diameter mm	Copper index (kg/km)	Weight (kg/km)
PVC sheath						
2170485	ETHERLINE® FD CAT.6 _A	4x2xAWG24/7	1.3	8.9	44	88
PUR outer sheath, halogen-free						
2170484	ETHERLINE® FD P CAT.6 _A	4x2xAWG24/7	1.3	8.9	44	90

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16