

ETHERLINE® TORSION Cat.6A

Highly flexible application

Industrial Ethernet cable Cat.6A for torsion stress applications ($\pm 180^\circ$)

4 pairs, PVC or PUR jacket with UL approval, design 4x2xAWG24/7, for PROFINET Type C

Info

Industrial Ethernet Cable, 4-pair, suitable for torsion stress

Cat.6_A acc. to ISO/IEC 11801

For PROFINET applications



Supplementary automation components from Lapp



Suitable for outdoor use



Mechanical resistance



Robust



Interference signals



Torsion-resistant



UV-resistant

Benefits

Many applications with Industrial Ethernet, e.g. PROFINET, i.e. fixed installation, flexible use as well as TORSION.

4pair: 100Mbit/s up to 10 Gbit/s for Industrial Ethernet

Premium screening against electromagnetic interference

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ETHERLINE® TORSION Cat.6A

Can be used for Industrial Ethernet in harsh industrial environments

Application range

Suitable for torsional applications which are typical for the loop in wind turbine generators (WTG)
Can be used for Industrial Ethernet in harsh industrial environments
suitable for EtherCAT and EtherNet/IP applications

Product features

PUR version is halogen-free according to VDE 0472-815
Oil-resistant acc. IEC 60811-2-1
Cable suitable for high torsion stress. Tested with more than 1 million bending cycles and a right/left movement of 180° per metre.
Meets the requirements according to CAT.6A, ISO/IEC 11801 and EN 50173

Norm references / Approvals

electrical requirements acc. to IEC 61156-6
PUR cable is UL/CSA-certified (CMX)
PUR versions: UL AWM Style 21576
PVC cable is UL/CSA-certified (CM)
Flame retardant acc. to IEC 60332-1-2

Product Make-up

7-wire tinned stranded copper conductor
Core insulation made of polyethylene (PE)
S/FTP: copper braid as overall screening and pair screening with aluminium compound foil
Outer sheath: PUR/PVC
Colour: green (based on RAL 6018)

Technical Data

| | |
|---------------------------|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000830 ETIM 5.0 Class-Description: Data cable |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000830 ETIM 6.0 Class-Description: Data cable |
| Minimum bending radius: | Fixed installation: 8 x cable diameter Flexing: 15 x outer diameter |
| Characteristic impedance: | nom. 100 Ω acc. to IEC 61156-6 |
| Temperature range: | Cable with PUR jacket Fixed installation: -40°C to +80°C Flexing: -30°C to +70°C Cable with PVC jacket Fixed installation: -40°C to +80°C Flexing: -10°C bis +70°C |

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

PROFINET® is a registered trademark of the PNO (PROFIBUS user organisation)

Detailed data sheets are available upon request. Please specify the type/dimensions of the required cable.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ETHERLINE® TORSION Cat.6A

UL certifications can be found in the data sheet.

ETHERLINE® TORSION Cat.6A

| Article number | Article designation | Number of pairs and AWG per conductor | Core diameter in mm | Outer diameter mm | Copper index (kg/km) | Weight (kg/km) |
|--------------------------------|--|---------------------------------------|---------------------|-------------------|----------------------|----------------|
| PVC jacket | | | | | | |
| 2170482 | ETHERLINE® TORSION Y CAT6 _A | 4 x 2 x AWG24/7 | 1.3 | 8.9 | 44 | 88 |
| PUR outer sheath, halogen-free | | | | | | |
| 2170483 | ETHERLINE® TORSION P CAT6 _A | 4 x 2 x AWG24/7 | 1.3 | 8.9 | 44 | 90 |

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16