

ETHERLINE® TORSION Cat.6A

Highly flexible application

Industrial Ethernet cable Cat.6A for torsion stress applications ($\pm 180^\circ$)


4 pairs, PVC or PUR jacket with UL approval, design 4x2xAWG24/7, for PROFINET Type C

Info

Industrial Ethernet Cable, 4-pair, suitable for torsion stress

Cat.6_A acc. to ISO/IEC 11801

For PROFINET applications



Supplementary automation components from Lapp



Suitable for outdoor use



Mechanical resistance



Robust



Interference signals



Torsion-resistant



UV-resistant

Benefits

Many applications with Industrial Ethernet, e.g. PROFINET, i.e. fixed installation, flexible use as well as TORSION.

4pair: 100Mbit/s up to 10 Gbit/s for Industrial Ethernet

Premium screening against electromagnetic interference

Can be used for Industrial Ethernet in harsh industrial environments

Last Update (22.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ETHERLINE® TORSION Cat.6A

Application range

Suitable for torsional applications which are typical for the loop in wind turbine generators (WTG)
Can be used for Industrial Ethernet in harsh industrial environments
suitable for EtherCAT and EtherNet/IP applications

Product features

PUR version is halogen-free according to VDE 0472-815

Oil-resistant acc. IEC 60811-2-1

Cable suitable for high torsion stress. Tested with more than 1 million bending cycles and a right/left movement of 180° per metre.

Meets the requirements according to CAT.6A, ISO/IEC 11801 and EN 50173

Norm references / Approvals

electrical requirements acc. to IEC 61156-6

PUR cable is UL/CSA-certified (CMX)

PUR versions: UL AWM Style 21576

PVC cable is UL/CSA-certified (CM)

Flame retardant acc. to IEC 60332-1-2

Product Make-up

7-wire tinned stranded copper conductor

Core insulation made of polyethylene (PE)

S/FTP: copper braid as overall screening and pair screening with aluminium compound foil

Outer sheath: PUR/PVC

Colour: green (based on RAL 6018)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000830 ETIM 5.0 Class-Description: Data cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000830 ETIM 6.0 Class-Description: Data cable
Minimum bending radius:	Fixed installation: 8 x cable diameter Flexing: 15 x outer diameter
Characteristic impedance:	nom. 100 Ω acc. to IEC 61156-6
Temperature range:	Cable with PUR jacket Fixed installation: -40 °C to +80 °C Flexing: -30 °C to +70 °C Cable with PVC jacket Fixed installation: -40 °C to +80 °C Flexing: -10 °C bis +70 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

PROFINET® is a registered trademark of the PNO (PROFIBUS user organisation)

Detailed data sheets are available upon request. Please specify the type/dimensions of the required cable.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

UL certifications can be found in the data sheet.

ETHERLINE® TORSION Cat.6A

Article number	Article designation	Number of pairs and AWG per conductor	Core diameter in mm	Outer diameter mm	Copper index (kg/km)	Weight (kg/km)
PVC jacket						
2170482	ETHERLINE® TORSION Y CAT6 _A	4 x 2 x AWG24/7	1.3	8.9	44	88
PUR outer sheath, halogen-free						
2170483	ETHERLINE® TORSION P CAT6 _A	4 x 2 x AWG24/7	1.3	8.9	44	90

Last Update (22.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16