

ETHERLINE® LAN 200 Cat.5e

Ethernet cable for Category 5e/ class D - verified up to 200 MHz

Data cable for Category 5e/ class D - verified up to 200 MHz

Info

CPR: Article number choice under www.lappkabel.com/cpr



Flame-retardant



Halogen-free



Interference signals

Benefits

LAN cables for structured building cabling according to EN 50173 and ISO/IEC 11801

Application range

Areas where the end device density is very high

For office wiring, administration and development buildings in the tertiary sector (floor wiring).

Cable length in tertiary area (horizontal area, floor) should not exceed a length of 100 m in accordance with the ISO/IEC 11801 and EN 50173 standards (90 m in cable duct + 10 m in working area)

Product features

Transfer of digital and analogue data signals

IEEE 802.3: 10/100/1000Base-T

Flame retardant acc. to IEC 60332-1-2

Norm references / Approvals

LAN CAT.5e cables from Lapp Kabel for "Structured Cabling Systems" meet the requirements in accordance with EIA/TIA-568 and TSB36, as well as ISO/IEC 11801 or EN 50173 (Class D).

Product Make-up

Solid conductor 4x2xAWG24/1

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ETHERLINE® LAN 200 Cat.5e

U/UTP: no overall or pair screening

F/UTP: foil screening as overall screening

SF/UTP: braid of tinned copper wire and plastic laminated aluminum foil as overall screening
outer sheath either as PVC (grey RAL 7035) or LSZH (orange RAL 2003)

Technical Data

Classification ETIM 6:	ETIM 6.0 Class-ID: EC000830 ETIM 6.0 Class-Description: Data cable
Minimum bending radius:	Fixed installation: 4 x outer diameter during installation: 8 x outer diameter
Characteristic impedance:	100 Ω \pm 15%
Temperature range:	During installation: 0 °C to +50 °C Fixed installation: -20 °C to +60 °C

Note

Packaging size: Drum

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ETHERLINE® LAN 200 Cat.5e

Article number	Article designation	Number of pairs and AWG per conductor	Core diameter in mm	Outer diameter mm	Colour	Copper index (kg/km)	Weight (kg/km)
2170951	UNITRONIC® LAN Cat.5e SF/UTP 4x2xAWG24	4 x 2 x AWG24/1	1.05	6.3	grey	28	46
LSZH							
2170952	ETHERLINE® LAN Cat.5e F/UTP 4x2xAWG24 LSZH	4 x 2 x AWG24/1	1.05	6.3	orange	18	40
2170953	UNITRONIC® LAN Cat.5e SF/UTP 4x2xAWG24 LSZH	4 x 2 x AWG24/1	1.05	6.4	orange	28	46
PVC							
2170950	ETHERLINE® LAN Cat.5e U/UTP 4x2x24AWG	4 x 2 x AWG24/1	0.9	5.1	grey	17	32

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16

ETHERLINE® LAN 200 Cat.5e

