

## UNITRONIC® LAN 500 Cat.6A

Ethernet cable for Category 6<sub>A</sub>/ class E<sub>A</sub> -verified up to 500 MHz

The LAN cable with a characteristic impedance of approximately 100 ohms is suitable for structured building wiring networks. It has solid core conductor and high-quality shielding.

### Info

CPR: Article number choice under [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)



Halogen-free



Interference signals

### Benefits

LAN cables for structured building cabling according to EN 50173 and ISO/IEC 11801

### Application range

Mainly used where the terminal density is very high, e.g. for wiring office, administration and development buildings in the tertiary area (floor wiring).

Cable length in tertiary area (horizontal area, floor) should not exceed a length of 100 m in accordance with the ISO/IEC 11801 and EN 50173 standards (90 m in cable duct + 10 m in working area)

### Product features

Transfer of digital and analogue data signals

Flame retardant acc. to IEC 60332-1-2

2170195

2170196: flame retardant acc. to IEC 60332-1-2 and IEC 60332-3-24

IEEE 802.3: 10/100/1000Base-T, 10GBase-T IEEE 802.5: ISDN; FDDI; ATM

### Norm references / Approvals

Class EA out of the standard ISO/IEC 11801 corresponds to Cat.6A

LAN Cat.6A cables from Lapp Kabel for "Structured Cabling Systems" meet the requirements in accordance with EIA/TIA-568 and TSB36, as well as ISO/IEC 11801 or EN 50173 (Class EA - permanent link).

### Product Make-up

Last Update (19.06.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## UNITRONIC® LAN 500 Cat.6A

Solid conductor

U/FTP: aluminium compound foil as pair screening

F/FTP: aluminium compound foil as overall screening and pair screening

S/FTP: copper braid as overall screening and pair screening with aluminium compound foil  
outer sheath either as PVC (color grey RAL1015) or LSZH (color orange RAL2003)

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000830 ETIM 5.0 Class-Description: Data cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000830 ETIM 6.0 Class-Description: Data cable
Minimum bending radius:	during installation: 8 x outer diameter Fixed installation: 4 x outer diameter
Characteristic impedance:	100 $\Omega$ $\pm$ 15%
Temperature range:	Fixed installation: -20 °C to +60 °C Flexing: 0 °C to +50 °C

### Note

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: [www.lappkabel.de/en/cable-standardlengths](http://www.lappkabel.de/en/cable-standardlengths)

Packaging size: Coil 100 m; Drum (500; 1000) m

CAT.6a is available as a draft

Detailed data sheets are available upon request. Please specify the type/dimensions of the required cable.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**UNITRONIC® LAN 500 Cat.6A**

Article number	Article designation	Number of pairs and AWG per conductor	Outer diameter mm	Copper index (kg/km)	Weight (kg/km)
PVC version					
2170143	UNITRONIC® LAN 500 S/FTP Cat.6A	4 x 2 x AWG23/1	7.7	27	58
Halogen-free versions					
2170195	UNITRONIC® LAN 500 U/FTP Cat.6A LSZH	4 x 2 x AWG23/1	7.4	21	52
2170196	UNITRONIC® LAN 500 F/FTP Cat.6A LSZH	4 x 2 x AWG23/1	7.6	22	56

Last Update (19.06.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16