


## UNITRONIC® LiYCY-CY

Screened data transmission cable with individually screened cores

UNITRONIC® LiYCY-CY: Low-frequency PVC data cable, DIN 47100 color coded, Single-core screen, Overall screen, Flexible, Flame retardant, Instrumentation Control



Interference signals

### Benefits

Overall braid minimises electrical interference  
Individually screened cores minimise crosstalk between cables routed in parallel

### Application range

When a lossless transmission of data has to be guaranteed in fields with strong interference, cables with individually-screened cores and an additional overall screening are used  
Dry or damp rooms

### Product features

Wire-screen can be used as outer conductor  
The cable remains flexible despite multiple screening  
Flame-retardant according IEC 60332-1-2

### Norm references / Approvals

Based on VDE 0812

### Product Make-up

Fine-wire strand made of bare copper wires  
Core insulation made of PVC  
Tinned-copper braiding for each core  
Inner sheath made of PVC over each screened core

Last Update (10.04.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## UNITRONIC® LiYCY-CY

Tinned-copper braiding  
Outer sheath made of PVC  
Outer sheath colour: grey (similar to pebble grey/ RAL 7032)

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class-Description: Control cable
Core identification code:	DIN 47100, refer to Appendix T9
Mutual capacitance:	Approx. 230 nF/km
Inductivity:	Approx. 0.2 mH/km
Conductor stranding:	Stranded conductor, fine-wire
Minimum bending radius:	Occasional flexing: 15 x outer diameter Fixed installation: 7.5 x outer diameter
Temperature range:	Occasional flexing: -5 °C to +70 °C Fixed installation: -40 °C to +80 °C

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: [www.lappkabel.de/en/cable-standardlengths](http://www.lappkabel.de/en/cable-standardlengths)

Packaging size: coil  $\leq$  30 kg or  $\leq$  250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**UNITRONIC® LiYCY-CY**

Article number	Number of cores and mm <sup>2</sup> per conductor	Outer diameter [mm]	Copper index [kg/km]	Weight [kg/km]
UNITRONIC® LiYCY-CY				
0032302	2 x 0.25	6.9	41.5	69
0032303	3 x 0.25	7.2	53	106
0032304	4 x 0.25	7.8	65	130
0032305	5 x 0.25	8.5	78	161

Last Update (10.04.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16