

UNITRONIC® Li2YCYv (TP)

Screened data transmission cable mit PE core insulation, reinforced outer sheath and twisted pairs

UNITRONIC® Li2YCYv (TP): Low-capacitance screened PVC data cable, DIN 47100 coded Twisted PE pairs, Reinforced black jacket/ Outdoor laying, RS422/ RS485 wiring

Info

Cables for RS485/RS422



Interference signals

Benefits

Overall braid minimises electrical interference

Decoupling of circuits by means of twisted-pair (TP) design (crosstalk effects)

Application range

Particularly suitable for wiring data systems with transmission rates up to 10 Megabits per second, and is qualified for the RS422 and RS485 interfaces.

For fixed and limited flexible installation

Can be used in dry or damp rooms

Signal-, control- and measuring cable, for transmission of low, sensitive signals and high bit rates

UNITRONIC®

Li2YCYv (TP) with its reinforced, nominal/ minimum average wall thickness of at least 1.8 mm of the black outer sheath (Yv) is designed for indoor and outdoor use as well as for applications where a reinforced outer sheath may turn out to be advantageous

Product features

Flame-retardant according IEC 60332-1-2

Norm references / Approvals

Based on VDE 0812

Last Update (22.10.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

UNITRONIC® Li2YCYv (TP)

Product Make-up

7-wire bare stranded copper conductor
Core insulation made of polyethylene (PE)
TP structure
Tinned-copper braiding
Wall thickness of the outer sheath is increased ("Yv")
Outer sheath colour: black (RAL 9005)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class-Description: Control cable
Core identification code:	DIN 47100, refer to Appendix T9
Mutual capacitance:	At 800 Hz: max. 60 nF/km
Inductivity:	approx. 0.65 mH/km
Conductor stranding:	Stranded conductor, based on VDE 0881, 7-wire
Minimum bending radius:	Occasional flexing: 15 x outer diameter Fixed installation: 6 x outer diameter
Short-range crosstalk attenuation:	Up to 1 MHz min. 50 dB Up to 10 MHz min. 40 dB
Test voltage:	Core/core: 2000 V Core/screen: 1000 V
Characteristic impedance:	100 ± 15 Ohm (> 1 MHz)
Temperature range:	Occasional flexing: -5°C to +70°C Fixed installation: -40°C to +80°C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

UNITRONIC® Li2YCYv (TP)

Article number	Number of pairs and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
UNITRONIC® Li2YCYv (TP), strengthened outer sheath "Yv", and black for outdoor installation/ technical UV resistance, 7-wire				
0031350	2 x 2 x 0.22	8.1	24.2	79
0031351	3 x 2 x 0.22	8.4	28.6	93
0031352	4 x 2 x 0.22	8.9	34.2	100
0031353	8 x 2 x 0.22	10.7	70	156
0031354	10 x 2 x 0.22	12	76	185
0031365	1 x 2 x 0.34	7.4	20	69
0031355	2 x 2 x 0.34	9.3	34.1	102
0031356	3 x 2 x 0.34	10	43	117
0031357	4 x 2 x 0.34	10.3	52.8	130
0031358	8 x 2 x 0.34	12.6	85.8	206
0031366	1 x 2 x 0.5	7.9	29	79
0031360	2 x 2 x 0.5	10.1	37	120
0031361	3 x 2 x 0.5	10.9	55	142
0031362	4 x 2 x 0.5	11.2	60	160
0031363	8 x 2 x 0.5	13.9	113.3	251
0031364	10 x 2 x 0.5	16	148	303

Last Update (22.10.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16