


UNITRONIC® SENSOR master cable

Rational wiring for S/A boxes with detachable master cable connection. Outer sheath halogen free, Drag chain suitable. Customised construction can be supported.

Info

Customised construction can be supported



Supplementary automation components from Lapp



Flame-retardant



Halogen-free



Power chain



UV-resistant

Benefits

Cost efficient and rational wiring for S/A boxes with detachable master cable connection
Can be used universally for S/A installations

Application range

Automation technology
Mechanical engineering
Plant engineering
Tool shop
Automotive industry

UNITRONIC® SENSOR master cable

Product features

Cores for Power Supply:
3 x 0.75 mm² and 3 x 1.0 mm²
Cores for Signalling cable:
4 x 0.34 mm², 8 x 0.5 mm², 16 x 0.5 mm²
Suitable for drag chains
Halogen-free according to VDE 0472-815
Flame-retardant according to UL 1581 FT-2

Norm references / Approvals

UL-AWM-Style 21198 (80 °C / 300 V)

Product Make-up

Fine-wire, bare copper strand
Single wire diameter:
0.34 mm² = (43 x 0.10 mm)
0.5 mm² = (19 x 0.18 mm)
0.75 mm² = (21 x 0.205 mm)
1.0 mm² = (55 x 0.15 mm)
Core insulation: PP
Outer sheath: PUR, black

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001578 ETIM 5.0 Class-Description: Flexible cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001578 ETIM 6.0 Class-Description: Flexible cable
Conductor stranding:	Stranded conductor, fine-wire
Minimum bending radius:	Flexing: 10 x outer diameter
Temperature range:	Fixed installation: -40 °C to +80 °C Flexing: -5 °C to +80 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Packaging size: Coil 100m

Cables are printed

Other variations are available upon request.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

For detailed technical information please refer to the data sheet

UNITRONIC® SENSOR master cable

Article number	Article designation	Dimensions (mm ²)	Outer diameter [mm]	Core/outer sheath material	Copper index [kg/km]
UNITRONIC® SENSOR COMBI					
7038880	Li9Y11Y	3 x 0.75 + 4 x 0.34	6.6	PP/PUR	34.5
7038881	Li9Y11Y	3 x 1.0 + 8 x 0.5	8.4	PP/PUR	67.2
7038882	Li9Y11Y	3 x 1.0 + 16 x 0.5	9.8	PP/PUR	105.6

UNITRONIC® SENSOR master cable