

## EPIC® POWER LS1.5 A6


Circular connectors for servomotors and power supply

EPIC® LS1.5 panel base for female contacts for connection with cable coupler

### Info

The contacts have to be ordered separately

Made in Germany



Mechanical and plant engineering



Wide clamping range



Mechanical resistance



Optimum strain relief



Robust



Interference signals



Waterproof

### Benefits

more power for servo motors

Vibration-proof rugged design

EMC version for cables with large cross-sections

### Application range

Plant engineering

Servo drives and servo assemblies

Last Update (25.07.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® POWER LS1.5 A6

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC002635 ETIM 5.0 Class-Description: Circular connector (industrial connector)
Classification ETIM 6:	ETIM 6.0 Class-ID: EC002635 ETIM 6.0 Class-Description: Circular connector (industrial connector)
Rated voltage (V):	630 V (3.6 mm contacts) 250 V (2 mm contacts)
Rated impulse voltage:	6 kV (3.6 mm contacts) 4 kV (2 mm contacts)
Rated current (A):	70 A (3.6-mm contacts) at 25 °C 30 A (2-mm contacts) at 25 °C
Pollution degree:	3
Contacts:	Gold-plated brass
Number of contacts:	3+PE+2(3.6mm/2mm) 3+PE+4(3.6mm/2mm)
Termination methods:	Crimp termination: 0.75 - 10 mm <sup>2</sup> (3.6 mm contacts) Crimp termination: 0.14 - 4.0 mm <sup>2</sup> (2 mm contacts)
Material:	Housing: nickel-plated zinc die-casting, nickel-plated brass Insert: PA, Seal: FPM
Protection rating:	IP 67
Cycle of mechanical operation:	50
Temperature range:	-20 °C to +125 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® POWER LS1.5 A6**

Article number	Article description	Fastening type	Pin configuration	Packaging unit
Type LS1.5 A6 for female contacts				
44429316	EPIC® POWER LS1.5 A6	Ø 4.2 mm (4x)	3+PE+2	1
44429317	EPIC® POWER LS1.5 A6	Ø 4.2 mm (4x)	3+PE+4	1

Last Update (25.07.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16