

EPIC® POWER LS1 A6 TWIST

Circular connectors for servomotors and power supply


EPIC® LS1 Power connector panel base with socket contacts and TWIST quick lock technology

Info

TWIST quick-lock technology

Connector with 1/4 turn safely locked

Made in Germany



Mechanical and plant engineering



Wind Energy



Good chemical resistance



Corrosion-resistant



Maximum vibration protection



Mechanical resistance



Assembly time



Optimum strain relief

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® POWER LS1 A6 TWIST



Space requirement



Robust



Interference signals



Waterproof



Variety of approval certifications

Benefits

Locking 70% faster

EMC-optimised design

Safety use in field environment by high protection class

Application range

Plant engineering

Servo drives and servo assemblies

Not pluggable with standard EPIC POWER LS1 counterparts type A1,A3,F6,F7,G4,G6

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002635

ETIM 5.0 Class-Description: Circular connector (industrial connector)

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002635

ETIM 6.0 Class-Description: Circular connector (industrial connector)

Rated voltage (V):

630 V (2 mm contacts)

250 V (1 mm contacts)

Rated impulse voltage:

6 kV (2 mm contacts)

4 kV (1 mm contacts)

Rated current (A):

26A/3+PE+4, 25A/5+PE (2mm contacts)

7 A (1 mm contacts)

Pollution degree:

3

Contact resistance:

< 4 mOhm

Contacts:

Gold-plated brass

Number of contacts:

3+PE+4(2mm/1mm)

5+PE(2mm)

Termination methods:

Crimp termination: 0.5 - 4.0 mm² (2 mm contacts)

Crimp termination: 0.14 - 1.0 mm² (1 mm contacts)

Material:

Housing: nickel-plated zinc die-casting, nickel-plated brass

Insert: PA,

Seal: FPM

Protection rating:

IP68 (10h/1m)

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® POWER LS1 A6 TWIST

Cycle of mechanical operation:	500
Temperature range:	-25°C up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® POWER LS1 A6 TWIST

Article number	Article description	Contacts included	Clamping range in mm	Fastening type	Pin configuration	Pieces / PU
Type LS1 A6 TWIST, front wall mounting, 6-pin, for female contacts						
24441291	LS1 A6	6	-	Ø 2.7 mm (4x)	5+PE	5
Type LS1 A6 TWIST, front wall mounting, 8-pin, for female contacts						
24441292	LS1 A6	8	-	Ø 2.7 mm (4x)	3+PE+4	5