

## EPIC® SIGNAL M17 A3

Circular connectors for servomotors and power supply


EPIC® M17 SIGNAL panel mount base angled, swivel

### Info

rotateable with 310° cable outlet

The contacts have to be ordered separately

Made in Germany



Mechanical and plant engineering



Mechanical resistance



Optimum strain relief



Space requirement



Interference signals



Waterproof

### Benefits

sensor/ ac

EMC protection

### Application range

Feedback / signal cables

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002635

ETIM 5.0 Class-Description: Circular connector (industrial connector)

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® SIGNAL M17 A3

Classification ETIM 6:	ETIM 6.0 Class-ID: EC002635 ETIM 6.0 Class-Description: Circular connector (industrial connector)
Rated voltage (V):	IEC: 48 V AC, 74 V DC
Rated impulse voltage:	1.5 kV
Rated current (A):	3.6 A
Pollution degree:	3
Contacts:	Gold-plated brass
Number of contacts:	Contacts: 8(1mm), 17(0.6mm)
Termination methods:	Crimp termination: 0.06 - 0.56 mm <sup>2</sup> (0,6mm contacts) Crimp termination: 0.06 - 1.0 mm <sup>2</sup> (1mm contacts)
Material:	Housing: nickel-plated zinc die-casting, nickel-plated brass Insert: PA, Seal: FPM
Protection rating:	IP 67
Cycle of mechanical operation:	100
Temperature range:	-40°C to +125°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® SIGNAL M17 A3**

Article number	Article description	Fastening type	Pin configuration	Pieces / PU
Type M17 A3, angled and rotateable				
44423114	EPIC® M17 female	Ø 2.7 mm (4x)	8	5
44423112	EPIC® M17 male	Ø 2.7 mm (4x)	8	5
44423115	EPIC® M17 female	Ø 2.7 mm (4x)	17	5
44423113	EPIC® M17 male	Ø 2.7 mm (4x)	17	5