EPIC® SIGNAL M23 G4

Circular connectors for Servo Cables and encoders

EPIC® M23 panel base for screw in with M25 thread

Info

For mounting in existing M25 threads or boreholes
Made in Germany



Mechanical and plant engineering

Wind Energy

Good chemical resistance

Robust

Interference signals

Benefits

Fast and easy assembly
Only one M25 bore hole necessary

Application range

Plant engineering
Servo drives and servo assemblies
Measurement and control technology

Technical Data

Last Update (28.07.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® SIGNAL M23 G4

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: nickel-plated zinc die-casting Sealing: FPM
Protection rating:	IP68 (10h/1m)
VDE-tested:	Certified production control: VDE-REG. no. C24 (according to EN 61984, SELV according to DIN VDE 0100-410 has to be guaranteed) UL File Number: E249137
Temperature range:	-25 °C up to +125 °C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2025 Lapp Group - Technical changes reserved

LAPP

EPIC® SIGNAL M23 G4

PRODUCT INFORMATION

Article number	Article	Coding	Fastening type	Pieces / PU
Type M23 G4 panel-mount box, front wall mounting				
44420032	M23 G4	black (N)	M25 x 1.5	5
44420031	M23 G4	black (N)	M25 x 1.5	20
44420033	M23 G4	red (+20°)	M25 x 1.5	20
44420030	M23 G4	blue (-20°)	M25 x 1.5	5

Last Update (28.07.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16