

## EPIC® MC Coax-Contacts

For inserts and modules of the EPIC® rectangular connectors

The internal conductor and external collar of the coaxial cable are bonded to the contact by soldering.

### Info

Selection between 50 and 75 ohms contacts

All contacts are high quality gold plated



### Product features

Solder termination: the inner conductor and the outer sleeve of the COAX cable are terminated by soldering

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.



## EPIC® MC Coax-Contacts

Article number	Article description	Contact type	Surface	For cable type	Packaging unit
Solder termination					
44429018	EPIC® MC SLEM 50Ohm RG58CU	male	Au	RG 58 CU	10
44429017	EPIC® MC BLEM 50Ohm RG58CU	female	Au	RG 58 CU	10
44429022	EPIC® MC SLEM 75Ohm RG187AU	male	Au	RG 187 AU	10
44429021	EPIC® MC BLEM 75Ohm RG187AU	female	Au	RG 187 AU	10
Solder/crimp termination					
11214200	MC SLEM COAX MALE	male	Au	RG 58	1
11219200	MC BLEM COAX FEMALE	female	Au	RG 58	1

Last Update (04.10.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16

**EPIC® MC Coax-Contacts**

