EPIC® H-A 10 SGR-LB

These connectors are attractive because of their compact housing.

The robust compact metal housing is ideal for use in rectangular connectors, for example in electronic laboratories.

Info
Protection rating UL50E tested





Mechanical and plant engineering

Mechanical resistance

Robust

Waterproof

Benefits
Small and space-saving for narrow available space

Application range
Machine and equipment manufacturing
Control engineering
Electronic laboratory

Product features
Surface-mount base
Single lever
1 cable entry

Technical Data

Last Update (25.01.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-A 10 SGR-LB

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2026 Lapp Group - Technical changes reserved

EPIC® H-A 10 SGR-LB

Article number	Article description	M	Packaging unit
19448100	H-A 10 SGR-LB M20	20	5
19448000	H-A 10 SGR-LB M25	25	5

Last Update (25.01.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16