

EPIC® H-A 10 SGRL-LB

These connectors are attractive because of their compact housing.

The compact base housing has a single lever and 2 cable entries. The housing is suitable for rectangular connectors and for use in control systems, for example.

Info
For easy introduction of two cables
Protection rating UL50E tested





Mechanical and plant engineering

Mechanical resistance

Robust

Waterproof

Benefits
Small and space-saving for narrow available space

Application range
Machine and equipment manufacturing
Control engineering
Electronic laboratory

Product features
Surface-mount base
Single lever
2 cable entries

Last Update (25.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-A 10 SGRL-LB

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2023 Lapp Group - Technical changes reserved

LAPP

PRODUCT INFORMATION

EPIC® H-A 10 SGRL-LB

Article number	Article description	M	PG	Pieces / PU
H-A housing: surface-mount base (2 cable entries, single lever)				
10450100	H-A 10 SGRL-LB 16	-	16	5
19450100	H-A 10 SGRL-LB M20	20	-	5

Last Update (25.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16